

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203512

Luminaire Tested: **LD6B70D010TE EU6B60709027 6LBMB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203512  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B70D010TE EU6B60709027 6LBMB1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH SPECULAR BLACK TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2534.6 lumens  
Efficiency: N/A  
Efficacy: 31.9 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.86  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 79.45  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203512

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBMB1

### Luminous Intensity Polar Plot





TEST NUMBER: P203512

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBMB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94		
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82		
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	76		
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72		
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67		
7	84	75	69	65	83	75	69	65	73	68	65	72	68	65	71	67	64	63		
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59		
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56		
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203512

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBMB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	289.5	11.4
10°-20°	714.4	28.2
20°-30°	860.5	33.9
30°-40°	544.3	21.5
40°-50°	124.6	4.9
50°-60°	1.4	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1864.4	73.6
0°-40°	2408.7	95.0
0°-60°	2534.6	100.0
0°-90°	2534.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2534.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3191	
5°	3119	289
15°	2549	714
25°	1907	860
35°	858	544
45°	138	125
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203512

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBMB1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3190.9
2.5°	3177.8
5°	3118.8
7.5°	3007.4
10°	2869.8
12.5°	2706.0
15°	2548.8
17.5°	2398.1
20°	2240.8
22.5°	2083.6
25°	1906.7
27.5°	1697.0
30°	1441.5
32.5°	1153.2
35°	858.3
37.5°	609.3
40°	412.8
42.5°	255.5
45°	137.6
47.5°	59.0
50°	13.1
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)