

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203615

Luminaire Tested: **LD6B70D010TE EU6B60709027 6LBMMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203615  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B70D010TE EU6B60709027 6LBMMW1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4669.0 lumens  
Efficiency: N/A  
Efficacy: 58.8 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.97  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 79.45  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203615

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBMMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P203615

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBMMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203615

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBMMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	321.8	6.9
10°-20°	862.0	18.5
20°-30°	1157.5	24.8
30°-40°	949.4	20.3
40°-50°	570.2	12.2
50°-60°	378.9	8.1
60°-70°	254.0	5.4
70°-80°	136.7	2.9
80°-90°	38.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2341.3	50.1
0°-40°	3290.8	70.5
0°-60°	4239.8	90.8
0°-90°	4669.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4669.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3484	
5°	3426	322
15°	3072	862
25°	2550	1157
35°	1507	949
45°	721	570
55°	419	379
65°	258	254
75°	129	137
85°	32	39
90°	0	



TEST NUMBER: P203615

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBMMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3483.8
2.5°	3458.1
5°	3425.9
7.5°	3355.0
10°	3271.3
12.5°	3168.3
15°	3071.7
17.5°	2955.8
20°	2839.9
22.5°	2711.1
25°	2550.1
27.5°	2356.9
30°	2099.3
32.5°	1809.5
35°	1506.9
37.5°	1249.3
40°	1030.3
42.5°	856.5
45°	721.2
47.5°	611.8
50°	534.5
52.5°	470.1
55°	418.6
57.5°	373.5
60°	334.9
62.5°	289.8
65°	257.6
67.5°	218.9
70°	186.7
72.5°	154.6
75°	128.8
77.5°	103.0
80°	77.3
82.5°	58.0
85°	32.2
87.5°	12.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)