

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205041

Luminaire Tested: **LD6B60D010TE EU6B60708035 6LBCSMMS1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205041
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60708035 6LBCSMMS1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6299.6 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205041

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBCSMMS1

Luminous Intensity Polar Plot





TEST NUMBER: P205041

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBCSMMS1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100		108	105	101	98		100	98	95		97	94	92		93	91	90
2	102	95	89	84		99	93	88	83		90	85	81		86	83	79		83	80	78
3	94	85	77	72		92	83	76	71		80	74	70		77	73	69		75	71	67
4	87	76	68	62		84	74	67	61		72	66	61		70	64	60		68	63	59
5	80	68	60	54		78	67	59	54		65	58	53		63	57	53		61	56	52
6	74	62	54	48		72	61	53	47		59	52	47		58	51	47		56	51	46
7	69	56	48	42		67	56	48	42		54	47	42		53	46	42		51	46	41
8	64	52	44	38		63	51	43	38		50	43	38		48	42	38		47	42	37
9	60	48	40	35		59	47	40	34		46	39	34		45	39	34		44	38	34
10	57	44	36	31		55	43	36	31		43	36	31		42	35	31		41	35	31

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205041

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBCSMMS1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	272.6	4.3
10°-20°	765.0	12.1
20°-30°	1117.3	17.7
30°-40°	1278.0	20.3
40°-50°	1228.2	19.5
50°-60°	948.4	15.1
60°-70°	529.3	8.4
70°-80°	154.1	2.4
80°-90°	6.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2155.0	34.2
0°-40°	3432.9	54.5
0°-60°	5609.5	89.0
0°-90°	6299.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6299.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2893	
5°	2868	273
15°	2714	765
25°	2428	1117
35°	2045	1278
45°	1601	1228
55°	1064	948
65°	530	529
75°	134	154
85°	4	7
90°	0	



TEST NUMBER: P205041

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBCSMMS1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2892.9
2.5°	2892.9
5°	2868.5
7.5°	2856.3
10°	2815.5
12.5°	2766.6
15°	2713.7
17.5°	2660.7
20°	2583.3
22.5°	2522.1
25°	2428.4
27.5°	2334.7
30°	2241.0
32.5°	2147.3
35°	2045.4
37.5°	1943.6
40°	1825.4
42.5°	1719.5
45°	1601.3
47.5°	1466.8
50°	1340.5
52.5°	1202.0
55°	1063.5
57.5°	920.8
60°	786.4
62.5°	651.9
65°	529.7
67.5°	415.6
70°	309.7
72.5°	216.0
75°	134.5
77.5°	69.3
80°	24.4
82.5°	8.1
85°	4.1
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)