

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205361

Luminaire Tested: **LD6B70D010TE EU6B60709027 6LBNLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205361  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B70D010TE EU6B60709027 6LBNLI1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4629.0 lumens  
Efficiency: N/A  
Efficacy: 58.3 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 79.45  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205361

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBNLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P205361

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBNL11

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |    |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     | 0   |    |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 |    |
| 1   | 114 | 112 | 109 | 107 | 112 | 109 | 107 | 106 | 105 | 104 | 102 | 102 | 101 | 99  | 98  | 97  | 96  | 95  | 95  |    |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 97  | 95  | 97  | 95  | 93  | 94  | 93  | 91  | 89  | 89  |    |
| 3   | 105 | 99  | 94  | 91  | 103 | 97  | 93  | 90  | 95  | 91  | 89  | 93  | 90  | 87  | 90  | 88  | 86  | 85  | 85  |    |
| 4   | 100 | 93  | 88  | 85  | 98  | 92  | 88  | 84  | 90  | 86  | 83  | 88  | 85  | 82  | 86  | 84  | 81  | 80  | 80  |    |
| 5   | 96  | 88  | 83  | 79  | 94  | 87  | 83  | 79  | 86  | 82  | 78  | 84  | 81  | 78  | 83  | 80  | 77  | 76  | 76  |    |
| 6   | 92  | 84  | 79  | 75  | 90  | 83  | 78  | 75  | 82  | 77  | 74  | 80  | 76  | 74  | 79  | 76  | 73  | 72  | 72  |    |
| 7   | 88  | 80  | 74  | 71  | 87  | 79  | 74  | 71  | 78  | 73  | 70  | 77  | 73  | 70  | 76  | 72  | 69  | 68  | 68  |    |
| 8   | 84  | 76  | 71  | 67  | 83  | 75  | 70  | 67  | 74  | 70  | 67  | 73  | 69  | 66  | 73  | 69  | 66  | 65  | 65  |    |
| 9   | 81  | 73  | 67  | 64  | 80  | 72  | 67  | 64  | 71  | 67  | 63  | 70  | 66  | 63  | 70  | 66  | 63  | 62  | 62  |    |
| 10  | 78  | 69  | 64  | 61  | 77  | 69  | 64  | 61  | 68  | 64  | 61  | 67  | 63  | 60  | 67  | 63  | 60  | 59  | 59  |    |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205361

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBNLI1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 876.2  | 18.9      |
| 10°-20°   | 1572.8 | 34.0      |
| 20°-30°   | 1271.6 | 27.5      |
| 30°-40°   | 732.6  | 15.8      |
| 40°-50°   | 154.9  | 3.3       |
| 50°-60°   | 13.3   | 0.3       |
| 60°-70°   | 6.7    | 0.1       |
| 70°-80°   | 0.9    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 3720.7 | 80.4      |
| 0°-40°    | 4453.3 | 96.2      |
| 0°-60°    | 4621.5 | 99.8      |
| 0°-90°    | 4629.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 4629.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 10539 |      |
| 5°  | 9818  | 876  |
| 15° | 5714  | 1573 |
| 25° | 2743  | 1272 |
| 35° | 1161  | 733  |
| 45° | 167   | 155  |
| 55° | 13    | 13   |
| 65° | 7     | 7    |
| 75° | 0     | 1    |
| 85° | 0     | 0    |
| 90° | 0     |      |



TEST NUMBER: P205361

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBNLI1

**CANDELA DISTRIBUTION (FULL):**

| 0°    |         |
|-------|---------|
| 0°    | 10539.3 |
| 2.5°  | 10412.4 |
| 5°    | 9818.4  |
| 7.5°  | 8964.0  |
| 10°   | 7916.1  |
| 12.5° | 6841.5  |
| 15°   | 5713.5  |
| 17.5° | 4625.5  |
| 20°   | 3831.2  |
| 22.5° | 3223.9  |
| 25°   | 2743.3  |
| 27.5° | 2336.1  |
| 30°   | 1969.0  |
| 32.5° | 1561.9  |
| 35°   | 1161.4  |
| 37.5° | 807.6   |
| 40°   | 527.3   |
| 42.5° | 320.4   |
| 45°   | 166.9   |
| 47.5° | 66.7    |
| 50°   | 20.0    |
| 52.5° | 20.0    |
| 55°   | 13.3    |
| 57.5° | 13.3    |
| 60°   | 6.7     |
| 62.5° | 6.7     |
| 65°   | 6.7     |
| 67.5° | 6.7     |
| 70°   | 6.7     |
| 72.5° | 0.0     |
| 75°   | 0.0     |
| 77.5° | 0.0     |
| 80°   | 0.0     |
| 82.5° | 0.0     |
| 85°   | 0.0     |
| 87.5° | 0.0     |
| 90°   | 0.0     |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)