

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203392

Luminaire Tested: **LD6B60D010TE EU6B60708035 6LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203392
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60708035 6LBMWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4834.9 lumens
Efficiency: N/A
Efficacy: 77.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203392

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBMWH1

Luminous Intensity Polar Plot






TEST NUMBER: P203392

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	85	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	79	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	87	78	73	69	77	72	68		76	71	68		74
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70
8	80	70	64	60	78	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203392

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	551.4	11.4
10°-20°	1353.7	28.0
20°-30°	1566.3	32.4
30°-40°	1001.2	20.7
40°-50°	283.9	5.9
50°-60°	50.7	1.0
60°-70°	20.7	0.4
70°-80°	7.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3471.5	71.8
0°-40°	4472.7	92.5
0°-60°	4807.2	99.4
0°-90°	4834.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4834.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6032	
5°	5924	551
15°	4855	1354
25°	3456	1566
35°	1580	1001
45°	330	284
55°	47	51
65°	20	21
75°	7	7
85°	0	0
90°	0	



TEST NUMBER: P203392

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBMWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	6031.8
2.5°	6025.0
5°	5924.2
7.5°	5742.6
10°	5487.1
12.5°	5191.2
15°	4855.0
17.5°	4505.3
20°	4162.4
22.5°	3826.2
25°	3456.3
27.5°	3052.9
30°	2602.3
32.5°	2098.0
35°	1580.2
37.5°	1143.1
40°	793.5
42.5°	524.5
45°	329.5
47.5°	195.0
50°	114.3
52.5°	67.2
55°	47.1
57.5°	40.3
60°	33.6
62.5°	26.9
65°	20.2
67.5°	13.4
70°	13.4
72.5°	6.7
75°	6.7
77.5°	6.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)