

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203301

Luminaire Tested: **LD6B70D010TE EU6B60708030 6LBMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203301  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B70D010TE EU6B60708030 6LBMH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5180.9 lumens  
Efficiency: N/A  
Efficacy: 65.2 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 79.45  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203301

CATALOG NUMBER: LD6B70D010TE EU6B60708030 6LBMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P203301

CATALOG NUMBER: LD6B70D010TE EU6B60708030 6LBMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92																			
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72																			
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53																			
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49																			
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203301

CATALOG NUMBER: LD6B70D010TE EU6B60708030 6LBMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	468.8	9.0
10°-20°	1212.7	23.4
20°-30°	1571.4	30.3
30°-40°	1166.6	22.5
40°-50°	492.5	9.5
50°-60°	174.9	3.4
60°-70°	67.5	1.3
70°-80°	23.4	0.5
80°-90°	3.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3252.9	62.8
0°-40°	4419.6	85.3
0°-60°	5087.0	98.2
0°-90°	5180.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5180.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5127	
5°	5016	469
15°	4328	1213
25°	3485	1571
35°	1850	1167
45°	607	492
55°	185	175
65°	67	68
75°	22	23
85°	0	3
90°	0	



TEST NUMBER: P203301

CATALOG NUMBER: LD6B70D010TE EU6B60708030 6LBMH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5127.0
2.5°	5112.2
5°	5016.1
7.5°	4875.5
10°	4705.3
12.5°	4520.4
15°	4328.0
17.5°	4113.5
20°	3921.1
22.5°	3721.4
25°	3484.6
27.5°	3159.1
30°	2774.4
32.5°	2323.1
35°	1849.6
37.5°	1450.1
40°	1102.4
42.5°	821.2
45°	606.7
47.5°	443.9
50°	325.5
52.5°	244.1
55°	185.0
57.5°	140.6
60°	111.0
62.5°	81.4
65°	66.6
67.5°	51.8
70°	37.0
72.5°	29.6
75°	22.2
77.5°	14.8
80°	7.4
82.5°	7.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)