

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204434

Luminaire Tested: **LD6B70D010TE EU6B60708030 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204434
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60708030 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6772.5 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204434

CATALOG NUMBER: LD6B70D010TE EU6B60708030 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P204434

CATALOG NUMBER: LD6B70D010TE EU6B60708030 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88			88																
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			76																
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66			66																
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			57																
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50			50																
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45			45																
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40			40																
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36			36																
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32			32																
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30			30																

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204434

CATALOG NUMBER: LD6B70D010TE EU6B60708030 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	296.1	4.4
10°-20°	831.3	12.3
20°-30°	1212.5	17.9
30°-40°	1382.6	20.4
40°-50°	1326.3	19.6
50°-60°	1015.8	15.0
60°-70°	557.4	8.2
70°-80°	148.2	2.2
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2339.9	34.6
0°-40°	3722.5	55.0
0°-60°	6064.6	89.5
0°-90°	6772.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6772.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3145	
5°	3121	296
15°	2950	831
25°	2633	1212
35°	2211	1383
45°	1723	1326
55°	1138	1016
65°	561	557
75°	130	148
85°	0	2
90°	0	



TEST NUMBER: P204434

CATALOG NUMBER: LD6B70D010TE EU6B60708030 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	3145.4
2.5°	3137.3
5°	3121.1
7.5°	3096.7
10°	3064.2
12.5°	3007.3
15°	2950.4
17.5°	2885.4
20°	2812.2
22.5°	2722.8
25°	2633.4
27.5°	2544.0
30°	2430.2
32.5°	2324.5
35°	2210.7
37.5°	2097.0
40°	1983.2
42.5°	1861.3
45°	1723.1
47.5°	1584.9
50°	1438.6
52.5°	1284.2
55°	1137.9
57.5°	991.6
60°	837.2
62.5°	690.9
65°	560.8
67.5°	430.8
70°	317.0
72.5°	211.3
75°	130.0
77.5°	56.9
80°	16.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)