

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203804

Luminaire Tested: **LD6B60D010TE EU6B60708035 6LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203804
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60708035 6LBNWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4126.2 lumens
Efficiency: N/A
Efficacy: 66.0 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203804

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBNWH1

Luminous Intensity Polar Plot






TEST NUMBER: P203804

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	111	109	107	112	109	107	105		105	104	102			101	100	99			94
2	109	104	101	97	107	103	99	96		99	97	94			96	94	92			89
3	104	98	93	90	102	97	92	89		94	91	88			92	89	86			83
4	99	92	87	83	97	91	86	83		89	85	82			87	84	81			79
5	95	87	82	78	93	86	81	77		84	80	77			83	79	76			74
6	91	82	77	73	89	82	76	73		80	76	72			79	75	72			70
7	87	78	73	69	85	77	72	69		76	72	68			75	71	68			66
8	83	74	69	65	82	74	68	65		73	68	65			72	67	64			63
9	79	71	65	62	78	70	65	61		69	65	61			68	64	61			60
10	76	67	62	58	75	67	62	58		66	61	58			65	61	58			57

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203804

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	685.8	16.6
10°-20°	1317.7	31.9
20°-30°	1197.9	29.0
30°-40°	726.1	17.6
40°-50°	165.3	4.0
50°-60°	21.1	0.5
60°-70°	9.5	0.2
70°-80°	2.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3201.4	77.6
0°-40°	3927.6	95.2
0°-60°	4114.0	99.7
0°-90°	4126.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4126.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8101	
5°	7638	686
15°	4746	1318
25°	2597	1198
35°	1151	726
45°	182	165
55°	21	21
65°	7	9
75°	0	3
85°	0	0
90°	0	



TEST NUMBER: P203804

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	8101.1
2.5°	8002.8
5°	7637.8
7.5°	7048.1
10°	6296.9
12.5°	5517.7
15°	4745.5
17.5°	4043.5
20°	3453.8
22.5°	2976.5
25°	2597.4
27.5°	2260.4
30°	1930.5
32.5°	1544.4
35°	1151.3
37.5°	807.3
40°	533.5
42.5°	329.9
45°	182.5
47.5°	84.2
50°	35.1
52.5°	28.1
55°	21.1
57.5°	21.1
60°	14.0
62.5°	14.0
65°	7.0
67.5°	7.0
70°	7.0
72.5°	7.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)