

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204733

Luminaire Tested: **LD6B60D010TE EU6B60708035 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204733
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60708035 6LBPSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6652.4 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204733

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBPSMW1

Luminous Intensity Polar Plot






TEST NUMBER: P204733

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86						
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74						
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63						
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54						
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47						
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42						
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37						
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33						
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30						
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27						

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204733

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	254.0	3.8
10°-20°	723.9	10.9
20°-30°	1090.2	16.4
30°-40°	1297.3	19.5
40°-50°	1294.9	19.5
50°-60°	1053.1	15.8
60°-70°	647.9	9.7
70°-80°	251.0	3.8
80°-90°	40.2	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2068.1	31.1
0°-40°	3365.3	50.6
0°-60°	5713.3	85.9
0°-90°	6652.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6652.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2680	
5°	2672	254
15°	2570	724
25°	2373	1090
35°	2077	1297
45°	1683	1295
55°	1178	1053
65°	650	648
75°	229	251
85°	32	40
90°	0	



TEST NUMBER: P204733

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2680.3
2.5°	2684.2
5°	2672.4
7.5°	2656.6
10°	2636.9
12.5°	2601.4
15°	2569.9
17.5°	2522.6
20°	2471.4
22.5°	2424.1
25°	2372.8
27.5°	2301.9
30°	2230.9
32.5°	2163.9
35°	2077.2
37.5°	1982.6
40°	1895.9
42.5°	1789.5
45°	1683.1
47.5°	1568.7
50°	1446.6
52.5°	1320.4
55°	1178.5
57.5°	1040.6
60°	906.6
62.5°	776.5
65°	650.4
67.5°	532.1
70°	421.7
72.5°	319.3
75°	228.6
77.5°	149.8
80°	90.7
82.5°	55.2
85°	31.5
87.5°	15.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)