

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205447

Luminaire Tested: **LD6B60D010TE EU6B60708035 6LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205447
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60708035 6LBSLI1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6603.4 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205447

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205447

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	111	107	104	101	109	105	102	99		101	99	96			97	95	93			94
2	103	96	91	86	100	94	89	85		91	87	83			88	84	81			85
3	95	86	79	74	93	85	78	73		82	76	72			79	75	71			77
4	88	78	70	64	86	77	69	64		74	68	63			72	67	62			70
5	82	71	63	57	80	70	62	57		67	61	56			66	60	55			64
6	76	64	56	51	74	63	56	51		62	55	50			60	54	50			59
7	71	59	51	46	70	58	51	45		57	50	45			55	49	45			54
8	67	54	47	41	65	54	46	41		52	46	41			51	45	41			50
9	63	50	43	38	61	50	43	38		49	42	38			48	42	37			47
10	59	47	40	35	58	46	39	35		45	39	35			45	39	34			44

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205447

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	384.0	5.8
10°-20°	977.5	14.8
20°-30°	1246.6	18.9
30°-40°	1292.8	19.6
40°-50°	1191.2	18.0
50°-60°	896.0	13.6
60°-70°	483.7	7.3
70°-80°	129.7	2.0
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2608.1	39.5
0°-40°	3900.9	59.1
0°-60°	5988.1	90.7
0°-90°	6603.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6603.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4167	
5°	4104	384
15°	3487	978
25°	2708	1247
35°	2062	1293
45°	1550	1191
55°	1003	896
65°	484	484
75°	112	130
85°	0	2
90°	0	



TEST NUMBER: P205447

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBSLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	4167.1
2.5°	4153.0
5°	4103.9
7.5°	4012.7
10°	3851.4
12.5°	3690.0
15°	3486.6
17.5°	3297.2
20°	3100.8
22.5°	2897.3
25°	2707.9
27.5°	2525.5
30°	2357.1
32.5°	2202.8
35°	2062.5
37.5°	1929.2
40°	1802.9
42.5°	1669.6
45°	1550.4
47.5°	1417.1
50°	1283.8
52.5°	1143.5
55°	1003.2
57.5°	862.9
60°	729.6
62.5°	603.3
65°	484.1
67.5°	371.8
70°	273.6
72.5°	189.4
75°	112.2
77.5°	49.1
80°	14.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)