

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203513

Luminaire Tested: **LD6B70D010TE EU6B60709030 6LBMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203513
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60709030 6LBMB1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR BLACK TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2635.3 lumens
Efficiency: N/A
Efficacy: 33.2 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.86
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203513

CATALOG NUMBER: LD6B70D010TE EU6B60709030 6LBMB1

Luminous Intensity Polar Plot





TEST NUMBER: P203513

CATALOG NUMBER: LD6B70D010TE EU6B60709030 6LBMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94		
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82		
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	76		
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72		
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67		
7	84	75	69	65	83	75	69	65	73	68	65	72	68	65	71	67	64	63		
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59		
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56		
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203513

CATALOG NUMBER: LD6B70D010TE EU6B60709030 6LBMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	301.0	11.4
10°-20°	742.8	28.2
20°-30°	894.7	33.9
30°-40°	565.9	21.5
40°-50°	129.5	4.9
50°-60°	1.5	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1938.4	73.6
0°-40°	2504.3	95.0
0°-60°	2635.3	100.0
0°-90°	2635.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2635.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3318	
5°	3243	301
15°	2650	743
25°	1982	895
35°	892	566
45°	143	130
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203513

CATALOG NUMBER: LD6B70D010TE EU6B60709030 6LBMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3317.6
2.5°	3304.0
5°	3242.7
7.5°	3126.9
10°	2983.8
12.5°	2813.5
15°	2650.0
17.5°	2493.3
20°	2329.8
22.5°	2166.3
25°	1982.4
27.5°	1764.4
30°	1498.7
32.5°	1199.0
35°	892.4
37.5°	633.6
40°	429.2
42.5°	265.7
45°	143.1
47.5°	61.3
50°	13.6
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)