

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203719

Luminaire Tested: **LD6B70D010TE EU6B60709030 6LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203719
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60709030 6LBNH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3807.3 lumens
Efficiency: N/A
Efficacy: 47.9 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203719

CATALOG NUMBER: LD6B70D010TE EU6B60709030 6LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P203719

CATALOG NUMBER: LD6B70D010TE EU6B60709030 6LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87																			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81																			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75																			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70																			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65																			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61																			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58																			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54																			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203719

CATALOG NUMBER: LD6B70D010TE EU6B60709030 6LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	438.9	11.5
10°-20°	1046.6	27.5
20°-30°	1199.1	31.5
30°-40°	805.6	21.2
40°-50°	230.2	6.0
50°-60°	56.3	1.5
60°-70°	21.4	0.6
70°-80°	8.2	0.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2684.6	70.5
0°-40°	3490.2	91.7
0°-60°	3776.8	99.2
0°-90°	3807.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3807.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4881	
5°	4742	439
15°	3756	1047
25°	2617	1199
35°	1284	806
45°	264	230
55°	62	56
65°	21	21
75°	7	8
85°	0	1
90°	0	



TEST NUMBER: P203719

CATALOG NUMBER: LD6B70D010TE EU6B60709030 6LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	4880.6
2.5°	4845.9
5°	4741.7
7.5°	4554.3
10°	4325.2
12.5°	4033.6
15°	3755.9
17.5°	3464.3
20°	3172.7
22.5°	2895.0
25°	2617.3
27.5°	2360.5
30°	2061.9
32.5°	1666.2
35°	1284.4
37.5°	937.2
40°	645.7
42.5°	423.5
45°	263.8
47.5°	159.7
50°	97.2
52.5°	76.4
55°	62.5
57.5°	48.6
60°	34.7
62.5°	27.8
65°	20.8
67.5°	13.9
70°	13.9
72.5°	6.9
75°	6.9
77.5°	6.9
80°	6.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)