

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204319

Luminaire Tested: **LD6B60D010TE EU6B60708035 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204319
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60708035 6LBSWH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6413.9 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204319

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBSWH1

Luminous Intensity Polar Plot






TEST NUMBER: P204319

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	101		108	105	102	99		101	98	96		97	95	93		94	92	90
2	103	96	90	85		100	94	89	84		91	86	83		87	84	81		85	82	79
3	95	86	79	73		93	84	78	73		82	76	72		79	74	70		76	73	69
4	88	77	70	64		86	76	69	63		74	68	63		72	66	62		69	65	61
5	81	70	62	56		79	69	62	56		67	60	55		65	59	55		63	58	54
6	76	64	56	50		74	63	55	50		61	54	49		60	54	49		58	53	49
7	71	58	51	45		69	58	50	45		56	49	45		55	49	44		54	48	44
8	66	54	46	41		65	53	46	41		52	45	40		51	45	40		50	44	40
9	62	50	42	37		61	49	42	37		48	41	37		47	41	37		46	41	37
10	58	46	39	34		57	46	39	34		45	38	34		44	38	34		43	38	34

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204319

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	352.8	5.5
10°-20°	913.2	14.2
20°-30°	1194.4	18.6
30°-40°	1264.8	19.7
40°-50°	1179.6	18.4
50°-60°	893.4	13.9
60°-70°	483.9	7.5
70°-80°	129.8	2.0
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2460.4	38.4
0°-40°	3725.2	58.1
0°-60°	5798.3	90.4
0°-90°	6413.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6413.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3825	
5°	3769	353
15°	3264	913
25°	2597	1194
35°	2021	1265
45°	1537	1180
55°	1004	893
65°	484	484
75°	112	130
85°	0	2
90°	0	



TEST NUMBER: P204319

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBSWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	3825.2
2.5°	3811.2
5°	3769.1
7.5°	3677.8
10°	3558.5
12.5°	3418.1
15°	3263.7
17.5°	3088.3
20°	2933.8
22.5°	2758.4
25°	2596.9
27.5°	2435.5
30°	2281.1
32.5°	2147.7
35°	2021.4
37.5°	1895.1
40°	1775.7
42.5°	1656.4
45°	1537.1
47.5°	1403.8
50°	1270.4
52.5°	1137.0
55°	1003.7
57.5°	863.3
60°	730.0
62.5°	603.6
65°	484.3
67.5°	372.0
70°	273.7
72.5°	189.5
75°	112.3
77.5°	49.1
80°	14.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)