

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205243

Luminaire Tested: **LD6B60D010TE EU6B60708035 6LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205243
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60708035 6LBWL11
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6189.4 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205243

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBWLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205243

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	99		100	98	97		96
2	106	101	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	92	87	82	97	91	86	81	88	84	80		86	82	79		83
4	93	85	78	73	92	84	78	73	81	76	72		79	75	71		77
5	88	78	71	66	86	77	71	66	75	70	65		73	69	65		72
6	82	72	65	60	81	71	65	60	70	64	59		68	63	59		67
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	50	71	61	55	50	60	54	50		59	54	50		58
9	69	57	51	46	67	57	50	46	56	50	46		55	50	46		54
10	65	54	47	43	64	53	47	42	52	46	42		51	46	42		51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205243

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	373.0	6.0
10°-20°	1121.2	18.1
20°-30°	1690.1	27.3
30°-40°	1729.9	27.9
40°-50°	1007.8	16.3
50°-60°	231.6	3.7
60°-70°	28.5	0.5
70°-80°	7.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3184.3	51.4
0°-40°	4914.2	79.4
0°-60°	6153.5	99.4
0°-90°	6189.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6189.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3867	
5°	3888	373
15°	3972	1121
25°	3705	1690
35°	2807	1730
45°	1298	1008
55°	225	232
65°	21	28
75°	7	7
85°	0	0
90°	0	



TEST NUMBER: P205243

CATALOG NUMBER: LD6B60D010TE EU6B60708035 6LBWLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	3866.6
2.5°	3859.6
5°	3887.7
7.5°	3915.7
10°	3950.8
12.5°	3957.8
15°	3971.9
17.5°	3957.8
20°	3922.8
22.5°	3810.5
25°	3705.2
27.5°	3536.8
30°	3319.3
32.5°	3094.7
35°	2807.0
37.5°	2484.2
40°	2126.3
42.5°	1726.3
45°	1298.2
47.5°	905.3
50°	596.5
52.5°	378.9
55°	224.6
57.5°	119.3
60°	63.2
62.5°	35.1
65°	21.1
67.5°	21.1
70°	14.0
72.5°	7.0
75°	7.0
77.5°	7.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)