

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204440

Luminaire Tested: **LD6B70D010TE EU6B60709030 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204440
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60709030 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5783.8 lumens
Efficiency: N/A
Efficacy: 72.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204440

CATALOG NUMBER: LD6B70D010TE EU6B60709030 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P204440

CATALOG NUMBER: LD6B70D010TE EU6B60709030 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88	88	88	88
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76	76	76	76
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66	66	66	66
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57	57	57	57
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50	50	50	50
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45	45	45	45
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40	40	40	40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36	36	36	36
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32	32	32	32
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30	30	30	30

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204440

CATALOG NUMBER: LD6B70D010TE EU6B60709030 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.9	4.4
10°-20°	710.0	12.3
20°-30°	1035.5	17.9
30°-40°	1180.8	20.4
40°-50°	1132.7	19.6
50°-60°	867.5	15.0
60°-70°	476.0	8.2
70°-80°	126.6	2.2
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1998.3	34.6
0°-40°	3179.1	55.0
0°-60°	5179.3	89.5
0°-90°	5783.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5783.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2686	
5°	2665	253
15°	2520	710
25°	2249	1035
35°	1888	1181
45°	1472	1133
55°	972	867
65°	479	476
75°	111	127
85°	0	2
90°	0	



TEST NUMBER: P204440

CATALOG NUMBER: LD6B70D010TE EU6B60709030 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2686.3
2.5°	2679.3
5°	2665.4
7.5°	2644.6
10°	2616.9
12.5°	2568.3
15°	2519.7
17.5°	2464.2
20°	2401.7
22.5°	2325.3
25°	2249.0
27.5°	2172.6
30°	2075.4
32.5°	1985.2
35°	1888.0
37.5°	1790.8
40°	1693.7
42.5°	1589.6
45°	1471.5
47.5°	1353.5
50°	1228.6
52.5°	1096.7
55°	971.8
57.5°	846.8
60°	715.0
62.5°	590.0
65°	478.9
67.5°	367.9
70°	270.7
72.5°	180.5
75°	111.1
77.5°	48.6
80°	13.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)