

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204952

Luminaire Tested: **LD6B70D010TE EU6B60708035 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204952
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60708035 6LBCSMB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6746.2 lumens
Efficiency: N/A
Efficacy: 84.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204952

CATALOG NUMBER: LD6B70D010TE EU6B60708035 6LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P204952

CATALOG NUMBER: LD6B70D010TE EU6B60708035 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88			88
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			75
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65			65
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56			56
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49			49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43			43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39			39
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35			35
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31			31
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28			28

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204952

CATALOG NUMBER: LD6B70D010TE EU6B60708035 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	269.4	4.0
10°-20°	767.6	11.4
20°-30°	1153.9	17.1
30°-40°	1369.2	20.3
40°-50°	1354.9	20.1
50°-60°	1064.3	15.8
60°-70°	596.7	8.8
70°-80°	167.5	2.5
80°-90°	2.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2191.0	32.5
0°-40°	3560.2	52.8
0°-60°	5979.4	88.6
0°-90°	6746.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6746.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2849	
5°	2844	269
15°	2723	768
25°	2505	1154
35°	2196	1369
45°	1765	1355
55°	1199	1064
65°	595	597
75°	145	168
85°	0	3
90°	0	



TEST NUMBER: P204952

CATALOG NUMBER: LD6B70D010TE EU6B60708035 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2848.7
2.5°	2839.0
5°	2843.8
7.5°	2819.7
10°	2790.6
12.5°	2756.8
15°	2722.9
17.5°	2679.4
20°	2621.4
22.5°	2563.3
25°	2505.3
27.5°	2442.4
30°	2360.2
32.5°	2278.0
35°	2195.8
37.5°	2099.0
40°	1987.8
42.5°	1881.4
45°	1765.3
47.5°	1634.7
50°	1499.3
52.5°	1344.5
55°	1199.4
57.5°	1035.0
60°	880.2
62.5°	740.0
65°	594.9
67.5°	469.1
70°	348.2
72.5°	237.0
75°	145.1
77.5°	72.5
80°	19.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)