

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205054

Luminaire Tested: **LD6B70D010TE EU6B60708035 6LBCSMMS1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205054  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B70D010TE EU6B60708035 6LBCSMMS1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7476.6 lumens  
Efficiency: N/A  
Efficacy: 94.1 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 79.45  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205054

CATALOG NUMBER: LD6B70D010TE EU6B60708035 6LBCSMMS1

### Luminous Intensity Polar Plot





TEST NUMBER: P205054

CATALOG NUMBER: LD6B70D010TE EU6B60708035 6LBCSMMS1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76			76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65			65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50			50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44			44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40			40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36			36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32			32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29			29

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205054

CATALOG NUMBER: LD6B70D010TE EU6B60708035 6LBCSMMS1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	323.6	4.3
10°-20°	907.9	12.1
20°-30°	1326.1	17.7
30°-40°	1516.7	20.3
40°-50°	1457.7	19.5
50°-60°	1125.6	15.1
60°-70°	628.3	8.4
70°-80°	182.8	2.4
80°-90°	7.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2557.6	34.2
0°-40°	4074.3	54.5
0°-60°	6657.6	89.0
0°-90°	7476.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7476.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3433	
5°	3404	324
15°	3221	908
25°	2882	1326
35°	2428	1517
45°	1900	1458
55°	1262	1126
65°	629	628
75°	160	183
85°	5	8
90°	0	



TEST NUMBER: P205054

CATALOG NUMBER: LD6B70D010TE EU6B60708035 6LBCSMMS1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3433.4
2.5°	3433.4
5°	3404.4
7.5°	3389.9
10°	3341.5
12.5°	3283.5
15°	3220.7
17.5°	3157.8
20°	3065.9
22.5°	2993.4
25°	2882.1
27.5°	2770.9
30°	2659.7
32.5°	2548.5
35°	2427.6
37.5°	2306.7
40°	2166.4
42.5°	2040.7
45°	1900.5
47.5°	1740.9
50°	1591.0
52.5°	1426.6
55°	1262.1
57.5°	1092.9
60°	933.3
62.5°	773.7
65°	628.7
67.5°	493.3
70°	367.5
72.5°	256.3
75°	159.6
77.5°	82.2
80°	29.0
82.5°	9.7
85°	4.8
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)