

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203398

Luminaire Tested: **LD6B60D010TE EU6B60709035 6LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203398
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709035 6LBMWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4083.8 lumens
Efficiency: N/A
Efficacy: 65.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203398

CATALOG NUMBER: LD6B60D010TE EU6B60709035 6LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203398

CATALOG NUMBER: LD6B60D010TE EU6B60709035 6LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	85	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	79	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	87	78	73	69	77	72	68		76	71	68		74
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70
8	80	70	64	60	78	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203398

CATALOG NUMBER: LD6B60D010TE EU6B60709035 6LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	465.7	11.4
10°-20°	1143.4	28.0
20°-30°	1322.9	32.4
30°-40°	845.6	20.7
40°-50°	239.8	5.9
50°-60°	42.8	1.0
60°-70°	17.5	0.4
70°-80°	6.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2932.1	71.8
0°-40°	3777.7	92.5
0°-60°	4060.3	99.4
0°-90°	4083.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4083.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5094	
5°	5004	466
15°	4101	1143
25°	2919	1323
35°	1335	846
45°	278	240
55°	40	43
65°	17	17
75°	6	6
85°	0	0
90°	0	



TEST NUMBER: P203398

CATALOG NUMBER: LD6B60D010TE EU6B60709035 6LBMWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	5094.5
2.5°	5088.8
5°	5003.6
7.5°	4850.3
10°	4634.5
12.5°	4384.6
15°	4100.6
17.5°	3805.3
20°	3515.6
22.5°	3231.6
25°	2919.3
27.5°	2578.5
30°	2198.0
32.5°	1772.0
35°	1334.7
37.5°	965.5
40°	670.2
42.5°	443.0
45°	278.3
47.5°	164.7
50°	96.6
52.5°	56.8
55°	39.8
57.5°	34.1
60°	28.4
62.5°	22.7
65°	17.0
67.5°	11.4
70°	11.4
72.5°	5.7
75°	5.7
77.5°	5.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)