

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202994

Luminaire Tested: **LD6B70D010TE EU6B60708040 6LBWGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202994  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B70D010TE EU6B60708040 6LBWGPH1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4887.0 lumens  
Efficiency: N/A  
Efficacy: 61.5 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.11  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 79.45  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202994

CATALOG NUMBER: LD6B70D010TE EU6B60708040 6LBWGP1

### Luminous Intensity Polar Plot





TEST NUMBER: P202994

CATALOG NUMBER: LD6B70D010TE EU6B60708040 6LBWGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82			
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74			
4	93	84	77	72	91	82	76	72	80	75	71	78	74	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	81	71	64	59	80	70	63	59	68	62	58	67	62	58	65	61	57	56			
7	76	65	58	53	75	65	58	53	63	57	53	62	57	53	61	56	52	51			
8	72	61	54	49	70	60	53	49	59	53	49	58	52	48	57	52	48	47			
9	68	57	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43			
10	64	53	46	42	63	52	46	42	51	45	41	51	45	41	50	45	41	40			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202994

CATALOG NUMBER: LD6B70D010TE EU6B60708040 6LBWGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	312.9	6.4
10°-20°	877.5	18.0
20°-30°	1255.4	25.7
30°-40°	1251.3	25.6
40°-50°	797.0	16.3
50°-60°	293.9	6.0
60°-70°	73.5	1.5
70°-80°	22.1	0.5
80°-90°	3.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2445.8	50.0
0°-40°	3697.1	75.7
0°-60°	4788.0	98.0
0°-90°	4887.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4887.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3322	
5°	3305	313
15°	3120	877
25°	2741	1255
35°	2035	1251
45°	1026	797
55°	311	294
65°	67	74
75°	17	22
85°	0	3
90°	0	



TEST NUMBER: P202994

CATALOG NUMBER: LD6B70D010TE EU6B60708040 6LBWGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3321.5
2.5°	3321.5
5°	3304.7
7.5°	3271.1
10°	3229.0
12.5°	3178.6
15°	3119.7
17.5°	3044.0
20°	2959.9
22.5°	2867.4
25°	2741.3
27.5°	2606.8
30°	2430.2
32.5°	2245.2
35°	2035.0
37.5°	1782.7
40°	1522.0
42.5°	1269.7
45°	1025.9
47.5°	807.3
50°	605.4
52.5°	445.7
55°	311.1
57.5°	201.8
60°	134.5
62.5°	92.5
65°	67.3
67.5°	50.5
70°	42.0
72.5°	25.2
75°	16.8
77.5°	16.8
80°	8.4
82.5°	8.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)