

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205453

Luminaire Tested: **LD6B60D010TE EU6B60709035 6LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205453
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709035 6LBSLI1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5577.3 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205453

CATALOG NUMBER: LD6B60D010TE EU6B60709035 6LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205453

CATALOG NUMBER: LD6B60D010TE EU6B60709035 6LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	111	107	104	101	109	105	102	99		101	99	96			97	95	93			89
2	103	96	91	86	100	94	89	85		91	87	83			88	84	81			77
3	95	86	79	74	93	85	78	73		82	76	72			79	75	71			68
4	88	78	70	64	86	77	69	64		74	68	63			72	67	62			60
5	82	71	63	57	80	70	62	57		67	61	56			66	60	55			53
6	76	64	56	51	74	63	56	51		62	55	50			60	54	50			47
7	71	59	51	46	70	58	51	45		57	50	45			55	49	45			43
8	67	54	47	41	65	54	46	41		52	46	41			51	45	41			39
9	63	50	43	38	61	50	43	38		49	42	38			48	42	37			36
10	59	47	40	35	58	46	39	35		45	39	35			45	39	34			33

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205453

CATALOG NUMBER: LD6B60D010TE EU6B60709035 6LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	324.3	5.8
10°-20°	825.6	14.8
20°-30°	1052.9	18.9
30°-40°	1091.9	19.6
40°-50°	1006.1	18.0
50°-60°	756.8	13.6
60°-70°	408.5	7.3
70°-80°	109.6	2.0
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2202.8	39.5
0°-40°	3294.7	59.1
0°-60°	5057.6	90.7
0°-90°	5577.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5577.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3520	
5°	3466	324
15°	2945	826
25°	2287	1053
35°	1742	1092
45°	1310	1006
55°	847	757
65°	409	409
75°	95	110
85°	0	2
90°	0	



TEST NUMBER: P205453

CATALOG NUMBER: LD6B60D010TE EU6B60709035 6LBSLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	3519.6
2.5°	3507.7
5°	3466.2
7.5°	3389.2
10°	3252.9
12.5°	3116.7
15°	2944.8
17.5°	2784.8
20°	2618.9
22.5°	2447.1
25°	2287.1
27.5°	2133.1
30°	1990.9
32.5°	1860.5
35°	1742.0
37.5°	1629.4
40°	1522.8
42.5°	1410.2
45°	1309.5
47.5°	1196.9
50°	1084.3
52.5°	965.8
55°	847.3
57.5°	728.8
60°	616.2
62.5°	509.6
65°	408.8
67.5°	314.0
70°	231.1
72.5°	160.0
75°	94.8
77.5°	41.5
80°	11.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)