

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205162

Luminaire Tested: **LD6B70D010TE EU6B60709040 6LBMLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205162  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B70D010TE EU6B60709040 6LBMLI1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5503.0 lumens  
Efficiency: N/A  
Efficacy: 69.3 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 79.45  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205162

CATALOG NUMBER: LD6B70D010TE EU6B60709040 6LBMLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P205162

CATALOG NUMBER: LD6B70D010TE EU6B60709040 6LBMLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94		
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82		
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76		
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71		
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67		
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63		
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205162

CATALOG NUMBER: LD6B70D010TE EU6B60709040 6LBMLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	634.4	11.5
10°-20°	1579.5	28.7
20°-30°	1836.1	33.4
30°-40°	1124.4	20.4
40°-50°	279.2	5.1
50°-60°	32.7	0.6
60°-70°	12.1	0.2
70°-80°	4.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4050.1	73.6
0°-40°	5174.5	94.0
0°-60°	5486.3	99.7
0°-90°	5503.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5503.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6887	
5°	6795	634
15°	5669	1580
25°	4063	1836
35°	1760	1124
45°	310	279
55°	28	33
65°	14	12
75°	7	5
85°	0	0
90°	0	



TEST NUMBER: P205162

CATALOG NUMBER: LD6B70D010TE EU6B60709040 6LBMLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6886.9
2.5°	6879.9
5°	6795.4
7.5°	6612.3
10°	6365.8
12.5°	6041.9
15°	5668.7
17.5°	5267.3
20°	4872.9
22.5°	4478.6
25°	4063.1
27.5°	3584.3
30°	3035.0
32.5°	2394.2
35°	1760.5
37.5°	1239.4
40°	845.0
42.5°	528.1
45°	309.8
47.5°	176.0
50°	91.5
52.5°	42.3
55°	28.2
57.5°	21.1
60°	21.1
62.5°	14.1
65°	14.1
67.5°	7.0
70°	7.0
72.5°	7.0
75°	7.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)