

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203192

Luminaire Tested: **LD6B60D010TE EU6B60709035 6LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203192
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709035 6LBWMW1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4889.8 lumens
Efficiency: N/A
Efficacy: 78.3 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203192

CATALOG NUMBER: LD6B60D010TE EU6B60709035 6LBWMW1

Luminous Intensity Polar Plot






TEST NUMBER: P203192

CATALOG NUMBER: LD6B60D010TE EU6B60709035 6LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	100		108	105	102	99		101	98	96		97	95	93		93	92	90
2	103	96	90	86		100	94	89	85		91	86	83		88	84	81		85	82	79
3	95	86	80	74		93	85	79	74		82	77	72		80	75	71		77	73	70
4	89	78	71	65		86	77	70	65		75	69	64		72	67	63		70	66	62
5	82	71	64	58		80	70	63	58		68	62	57		66	61	56		65	60	56
6	77	65	57	52		75	64	57	52		63	56	51		61	55	51		60	54	50
7	72	60	52	47		70	59	52	47		58	51	46		56	50	46		55	50	46
8	67	55	48	42		66	55	47	42		53	47	42		52	46	42		51	46	42
9	63	51	44	39		62	51	44	39		50	43	39		49	43	38		48	42	38
10	60	48	40	36		58	47	40	36		46	40	36		45	40	35		45	39	35

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203192

CATALOG NUMBER: LD6B60D010TE EU6B60709035 6LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	258.6	5.3
10°-20°	725.2	14.8
20°-30°	1044.9	21.4
30°-40°	1084.9	22.2
40°-50°	802.1	16.4
50°-60°	479.1	9.8
60°-70°	291.1	6.0
70°-80°	159.5	3.3
80°-90°	44.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2028.7	41.5
0°-40°	3113.6	63.7
0°-60°	4394.8	89.9
0°-90°	4889.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4889.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2746	
5°	2728	259
15°	2574	725
25°	2277	1045
35°	1750	1085
45°	1032	802
55°	522	479
65°	291	291
75°	148	160
85°	36	44
90°	0	



TEST NUMBER: P203192

CATALOG NUMBER: LD6B60D010TE EU6B60709035 6LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2745.9
2.5°	2745.9
5°	2728.1
7.5°	2704.4
10°	2668.8
12.5°	2627.3
15°	2573.9
17.5°	2514.6
20°	2455.3
22.5°	2372.3
25°	2277.4
27.5°	2176.6
30°	2046.1
32.5°	1915.6
35°	1749.6
37.5°	1577.6
40°	1387.8
42.5°	1203.9
45°	1031.9
47.5°	877.7
50°	741.3
52.5°	622.7
55°	521.9
57.5°	444.8
60°	379.6
62.5°	332.1
65°	290.6
67.5°	255.0
70°	219.4
72.5°	183.9
75°	148.3
77.5°	118.6
80°	89.0
82.5°	65.2
85°	35.6
87.5°	17.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)