

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204753

Luminaire Tested: **LD6B70D010TE EU6B60709040 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204753
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60709040 6LBPSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6679.7 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204753
CATALOG NUMBER: LD6B70D010TE EU6B60709040 6LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204753

CATALOG NUMBER: LD6B70D010TE EU6B60709040 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204753

CATALOG NUMBER: LD6B70D010TE EU6B60709040 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.0	3.8
10°-20°	726.9	10.9
20°-30°	1094.7	16.4
30°-40°	1302.6	19.5
40°-50°	1300.2	19.5
50°-60°	1057.4	15.8
60°-70°	650.5	9.7
70°-80°	252.0	3.8
80°-90°	40.4	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2076.6	31.1
0°-40°	3379.2	50.6
0°-60°	5736.8	85.9
0°-90°	6679.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6679.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2691	
5°	2683	255
15°	2580	727
25°	2383	1095
35°	2086	1303
45°	1690	1300
55°	1183	1057
65°	653	651
75°	230	252
85°	32	40
90°	0	



TEST NUMBER: P204753

CATALOG NUMBER: LD6B70D010TE EU6B60709040 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2691.3
2.5°	2695.2
5°	2683.3
7.5°	2667.5
10°	2647.7
12.5°	2612.1
15°	2580.4
17.5°	2533.0
20°	2481.5
22.5°	2434.0
25°	2382.6
27.5°	2311.3
30°	2240.1
32.5°	2172.8
35°	2085.7
37.5°	1990.7
40°	1903.7
42.5°	1796.8
45°	1690.0
47.5°	1575.2
50°	1452.5
52.5°	1325.8
55°	1183.4
57.5°	1044.8
60°	910.3
62.5°	779.7
65°	653.0
67.5°	534.3
70°	423.5
72.5°	320.6
75°	229.5
77.5°	150.4
80°	91.0
82.5°	55.4
85°	31.7
87.5°	15.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)