

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205042

Luminaire Tested: **LD6B60D010TE EU6B60708040 6LBCSMMS1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205042
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60708040 6LBCSMMS1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6362.3 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205042

CATALOG NUMBER: LD6B60D010TE EU6B60708040 6LBCSMMS1

Luminous Intensity Polar Plot






TEST NUMBER: P205042

CATALOG NUMBER: LD6B60D010TE EU6B60708040 6LBCSMMS1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100		108	105	101	98		100	98	95		97	94	92		93	91	90
2	102	95	89	84		99	93	88	83		90	85	81		86	83	79		83	80	78
3	94	85	77	72		92	83	76	71		80	74	70		77	73	69		75	71	67
4	87	76	68	62		84	74	67	61		72	66	61		70	64	60		68	63	59
5	80	68	60	54		78	67	59	54		65	58	53		63	57	53		61	56	52
6	74	62	54	48		72	61	53	47		59	52	47		58	51	47		56	51	46
7	69	56	48	42		67	56	48	42		54	47	42		53	46	42		51	46	41
8	64	52	44	38		63	51	43	38		50	43	38		48	42	38		47	42	37
9	60	48	40	35		59	47	40	34		46	39	34		45	39	34		44	38	34
10	57	44	36	31		55	43	36	31		43	36	31		42	35	31		41	35	31

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205042

CATALOG NUMBER: LD6B60D010TE EU6B60708040 6LBCSMMS1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	275.3	4.3
10°-20°	772.6	12.1
20°-30°	1128.5	17.7
30°-40°	1290.7	20.3
40°-50°	1240.4	19.5
50°-60°	957.8	15.1
60°-70°	534.6	8.4
70°-80°	155.6	2.4
80°-90°	6.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2176.4	34.2
0°-40°	3467.1	54.5
0°-60°	5665.4	89.0
0°-90°	6362.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6362.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2922	
5°	2897	275
15°	2741	773
25°	2453	1128
35°	2066	1291
45°	1617	1240
55°	1074	958
65°	535	535
75°	136	156
85°	4	7
90°	0	



TEST NUMBER: P205042

CATALOG NUMBER: LD6B60D010TE EU6B60708040 6LBCSMMS1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2921.7
2.5°	2921.7
5°	2897.0
7.5°	2884.7
10°	2843.5
12.5°	2794.2
15°	2740.7
17.5°	2687.2
20°	2609.0
22.5°	2547.3
25°	2452.6
27.5°	2358.0
30°	2263.3
32.5°	2168.7
35°	2065.8
37.5°	1962.9
40°	1843.6
42.5°	1736.6
45°	1617.2
47.5°	1481.4
50°	1353.9
52.5°	1214.0
55°	1074.0
57.5°	930.0
60°	794.2
62.5°	658.4
65°	535.0
67.5°	419.7
70°	312.7
72.5°	218.1
75°	135.8
77.5°	70.0
80°	24.7
82.5°	8.2
85°	4.1
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)