

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204954

Luminaire Tested: **LD6B70D010TE EU6B60708050 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204954
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60708050 6LBCSMB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6809.6 lumens
Efficiency: N/A
Efficacy: 85.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204954

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P204954

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88			88
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			75
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65			65
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56			56
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49			49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43			43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39			39
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35			35
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31			31
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28			28

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204954

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	272.0	4.0
10°-20°	774.8	11.4
20°-30°	1164.8	17.1
30°-40°	1382.1	20.3
40°-50°	1367.7	20.1
50°-60°	1074.3	15.8
60°-70°	602.3	8.8
70°-80°	169.1	2.5
80°-90°	2.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2211.6	32.5
0°-40°	3593.6	52.8
0°-60°	6035.6	88.6
0°-90°	6809.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6809.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2875	
5°	2870	272
15°	2748	775
25°	2529	1165
35°	2216	1382
45°	1782	1368
55°	1211	1074
65°	600	602
75°	146	169
85°	0	3
90°	0	



TEST NUMBER: P204954

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2875.4
2.5°	2865.7
5°	2870.5
7.5°	2846.1
10°	2816.8
12.5°	2782.7
15°	2748.5
17.5°	2704.6
20°	2646.0
22.5°	2587.4
25°	2528.8
27.5°	2465.3
30°	2382.4
32.5°	2299.4
35°	2216.4
37.5°	2118.7
40°	2006.5
42.5°	1899.0
45°	1781.9
47.5°	1650.1
50°	1513.4
52.5°	1357.2
55°	1210.7
57.5°	1044.7
60°	888.5
62.5°	746.9
65°	600.5
67.5°	473.5
70°	351.5
72.5°	239.2
75°	146.5
77.5°	73.2
80°	19.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)