

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204851

Luminaire Tested: **LD6B70D010TE EU6B60708050 6LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204851
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60708050 6LBCSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8059.3 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204851

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204851

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBSCMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87			
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74			
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63			
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55			
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48			
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42			
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33			
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30			
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204851

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBSCMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	311.9	3.9
10°-20°	887.9	11.0
20°-30°	1335.6	16.6
30°-40°	1582.9	19.6
40°-50°	1575.3	19.5
50°-60°	1269.9	15.8
60°-70°	768.2	9.5
70°-80°	285.2	3.5
80°-90°	42.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2535.4	31.5
0°-40°	4118.3	51.1
0°-60°	6963.4	86.4
0°-90°	8059.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8059.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3292	
5°	3277	312
15°	3145	888
25°	2901	1336
35°	2535	1583
45°	2051	1575
55°	1416	1270
65°	772	768
75°	259	285
85°	34	43
90°	0	



TEST NUMBER: P204851

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBCSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	3291.7
2.5°	3291.7
5°	3277.0
7.5°	3267.2
10°	3237.9
12.5°	3189.1
15°	3145.2
17.5°	3096.3
20°	3037.7
22.5°	2979.1
25°	2901.0
27.5°	2817.9
30°	2725.1
32.5°	2637.2
35°	2534.7
37.5°	2427.2
40°	2300.3
42.5°	2178.2
45°	2051.2
47.5°	1909.6
50°	1753.3
52.5°	1592.1
55°	1416.3
57.5°	1260.0
60°	1084.2
62.5°	927.9
65°	771.6
67.5°	625.1
70°	488.4
72.5°	366.3
75°	258.8
77.5°	166.0
80°	97.7
82.5°	58.6
85°	34.2
87.5°	14.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)