

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204128

Luminaire Tested: **LD6B70D010TE EU6B60708050 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60708050 6LBNMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5296.2 lumens
Efficiency: N/A
Efficacy: 66.7 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204128

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204128

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204128

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	403.3	7.6
10°-20°	1069.1	20.2
20°-30°	1427.3	26.9
30°-40°	1151.5	21.7
40°-50°	551.8	10.4
50°-60°	327.1	6.2
60°-70°	217.5	4.1
70°-80°	116.5	2.2
80°-90°	32.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2899.7	54.8
0°-40°	4051.2	76.5
0°-60°	4930.2	93.1
0°-90°	5296.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5296.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4344	
5°	4293	403
15°	3805	1069
25°	3123	1427
35°	1844	1152
45°	682	552
55°	362	327
65°	219	217
75°	109	117
85°	25	32
90°	0	



TEST NUMBER: P204128

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	4343.5
2.5°	4343.5
5°	4293.0
7.5°	4208.8
10°	4090.9
12.5°	3964.7
15°	3804.7
17.5°	3653.2
20°	3484.9
22.5°	3308.1
25°	3122.9
27.5°	2929.3
30°	2651.5
32.5°	2264.3
35°	1843.5
37.5°	1456.2
40°	1128.0
42.5°	875.4
45°	681.8
47.5°	538.7
50°	454.5
52.5°	404.0
55°	362.0
57.5°	328.3
60°	286.2
62.5°	252.5
65°	218.9
67.5°	185.2
70°	159.9
72.5°	134.7
75°	109.4
77.5°	84.2
80°	67.3
82.5°	50.5
85°	25.3
87.5°	8.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)