

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205258

Luminaire Tested: **LD6B70D010TE EU6B60708050 6LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205258
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60708050 6LBWL1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7414.7 lumens
Efficiency: N/A
Efficacy: 93.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205258

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBWLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205258

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92			
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76			
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69			
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63			
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205258

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	446.9	6.0
10°-20°	1343.1	18.1
20°-30°	2024.7	27.3
30°-40°	2072.4	27.9
40°-50°	1207.3	16.3
50°-60°	277.4	3.7
60°-70°	34.1	0.5
70°-80°	8.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3814.7	51.4
0°-40°	5887.1	79.4
0°-60°	7371.8	99.4
0°-90°	7414.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7414.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4632	
5°	4657	447
15°	4758	1343
25°	4439	2025
35°	3363	2072
45°	1555	1207
55°	269	277
65°	25	34
75°	8	9
85°	0	0
90°	0	



TEST NUMBER: P205258

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBWLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	4632.1
2.5°	4623.7
5°	4657.3
7.5°	4691.0
10°	4733.0
12.5°	4741.4
15°	4758.2
17.5°	4741.4
20°	4699.4
22.5°	4564.9
25°	4438.8
27.5°	4237.0
30°	3976.4
32.5°	3707.4
35°	3362.7
37.5°	2976.0
40°	2547.2
42.5°	2068.1
45°	1555.2
47.5°	1084.5
50°	714.6
52.5°	454.0
55°	269.0
57.5°	142.9
60°	75.7
62.5°	42.0
65°	25.2
67.5°	25.2
70°	16.8
72.5°	8.4
75°	8.4
77.5°	8.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)