

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202892

Luminaire Tested: **LD6B70D010TE EU6B60708050 6LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202892
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60708050 6LBWWH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6708.6 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202892

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202892

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92				92
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83				83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75				75
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68				68
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	63	62				62
6	82	71	64	59	80	71	64	59	69	63	59	67	62	58	66	61	58	56				56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51				51
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47				47
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43				43
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40				40

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202892

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	400.5	6.0
10°-20°	1191.0	17.8
20°-30°	1792.8	26.7
30°-40°	1833.1	27.3
40°-50°	1113.3	16.6
50°-60°	313.5	4.7
60°-70°	47.7	0.7
70°-80°	15.5	0.2
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3384.4	50.4
0°-40°	5217.4	77.8
0°-60°	6644.2	99.0
0°-90°	6708.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6708.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4167	
5°	4184	401
15°	4217	1191
25°	3914	1793
35°	2971	1833
45°	1431	1113
55°	312	314
65°	42	48
75°	17	15
85°	0	1
90°	0	



TEST NUMBER: P202892

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	4166.7
2.5°	4166.7
5°	4183.6
7.5°	4208.8
10°	4208.8
12.5°	4225.7
15°	4217.3
17.5°	4200.4
20°	4141.5
22.5°	4057.3
25°	3914.2
27.5°	3754.3
30°	3535.4
32.5°	3274.5
35°	2971.4
37.5°	2634.7
40°	2247.5
42.5°	1843.5
45°	1431.0
47.5°	1060.6
50°	749.2
52.5°	505.1
55°	311.5
57.5°	185.2
60°	92.6
62.5°	58.9
65°	42.1
67.5°	33.7
70°	25.3
72.5°	16.8
75°	16.8
77.5°	8.4
80°	8.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)