

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202898

Luminaire Tested: **LD6B70D010TE EU6B60709050 6LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202898
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60709050 6LBWWH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5647.4 lumens
Efficiency: N/A
Efficacy: 71.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202898

CATALOG NUMBER: LD6B70D010TE EU6B60709050 6LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202898

CATALOG NUMBER: LD6B70D010TE EU6B60709050 6LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92				92
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83				83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75				75
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68				68
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	63	62				62
6	82	71	64	59	80	71	64	59	69	63	59	67	62	58	66	61	58	56				56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51				51
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47				47
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43				43
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40				40

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202898

CATALOG NUMBER: LD6B70D010TE EU6B60709050 6LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	337.2	6.0
10°-20°	1002.6	17.8
20°-30°	1509.2	26.7
30°-40°	1543.1	27.3
40°-50°	937.2	16.6
50°-60°	263.9	4.7
60°-70°	40.1	0.7
70°-80°	13.1	0.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2849.0	50.4
0°-40°	4392.2	77.8
0°-60°	5593.3	99.0
0°-90°	5647.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5647.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3508	
5°	3522	337
15°	3550	1003
25°	3295	1509
35°	2501	1543
45°	1205	937
55°	262	264
65°	35	40
75°	14	13
85°	0	1
90°	0	



TEST NUMBER: P202898

CATALOG NUMBER: LD6B70D010TE EU6B60709050 6LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3507.7
2.5°	3507.7
5°	3521.8
7.5°	3543.1
10°	3543.1
12.5°	3557.3
15°	3550.2
17.5°	3536.0
20°	3486.4
22.5°	3415.5
25°	3295.1
27.5°	3160.4
30°	2976.2
32.5°	2756.5
35°	2501.4
37.5°	2218.0
40°	1892.0
42.5°	1551.9
45°	1204.7
47.5°	892.9
50°	630.7
52.5°	425.2
55°	262.2
57.5°	155.9
60°	77.9
62.5°	49.6
65°	35.4
67.5°	28.3
70°	21.3
72.5°	14.2
75°	14.2
77.5°	7.1
80°	7.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)