

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P295113

Luminaire Tested: **LD6B30DE010 EU6B30509030D2W 6LBM0B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P295113
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35128)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30DE010 EU6B30509030D2W 6LBM0B
Description: PORTFOLIO 6" D2W RN DOWNLIGHT, MEDIUM DISTRIBUTION WITH BLACK FINISH
Light Source: D2W 1800K-3000K CCT TUNING RANGE
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1092.2 lumens
Efficiency: N/A
Efficacy: 35.8 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.86
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 30.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P295113

CATALOG NUMBER: LD6B30DE010 EU6B30509030D2W 6LBM0B

Luminous Intensity Polar Plot





TEST NUMBER: P295113

CATALOG NUMBER: LD6B30DE010 EU6B30509030D2W 6LBM0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82			
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	76			
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	65	71	67	64	63			
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59			
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	89706
5°	88018
10°	81928
15°	74181
20°	67039
25°	59143
30°	46797
35°	29460
40°	15151
45°	5471
50°	568
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P295113

CATALOG NUMBER: LD6B30DE010 EU6B30509030D2W 6LBM0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.7	11.4
10°-20°	307.9	28.2
20°-30°	370.8	33.9
30°-40°	234.6	21.5
40°-50°	53.7	4.9
50°-60°	0.6	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	803.4	73.6
0°-40°	1038.0	95.0
0°-60°	1092.2	100.0
0°-90°	1092.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1092.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1375	
5°	1344	125
15°	1098	308
25°	822	371
35°	370	235
45°	59	54
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P295113

CATALOG NUMBER: LD6B30DE010 EU6B30509030D2W 6LBM0B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1375.0
2.5°	1369.4
5°	1344.0
7.5°	1296.0
10°	1236.7
12.5°	1166.1
15°	1098.3
17.5°	1033.4
20°	965.6
22.5°	897.9
25°	821.6
27.5°	731.3
30°	621.2
32.5°	496.9
35°	369.9
37.5°	262.6
40°	177.9
42.5°	110.1
45°	59.3
47.5°	25.4
50°	5.6
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)