

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205244

Luminaire Tested: **LD6B60D010TE EU6B60708040 6LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205244
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60708040 6LBWL11
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6251.0 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205244

CATALOG NUMBER: LD6B60D010TE EU6B60708040 6LBWLI1

Luminous Intensity Polar Plot






TEST NUMBER: P205244

CATALOG NUMBER: LD6B60D010TE EU6B60708040 6LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	99		100	98	97		96
2	106	101	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	92	87	82	97	91	86	81	88	84	80		86	82	79		83
4	93	85	78	73	92	84	78	73	81	76	72		79	75	71		77
5	88	78	71	66	86	77	71	66	75	70	65		73	69	65		72
6	82	72	65	60	81	71	65	60	70	64	59		68	63	59		67
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	50	71	61	55	50	60	54	50		59	54	50		58
9	69	57	51	46	67	57	50	46	56	50	46		55	50	46		54
10	65	54	47	43	64	53	47	42	52	46	42		51	46	42		51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205244

CATALOG NUMBER: LD6B60D010TE EU6B60708040 6LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	376.7	6.0
10°-20°	1132.3	18.1
20°-30°	1706.9	27.3
30°-40°	1747.1	27.9
40°-50°	1017.8	16.3
50°-60°	233.9	3.7
60°-70°	28.8	0.5
70°-80°	7.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3216.0	51.4
0°-40°	4963.1	79.4
0°-60°	6214.8	99.4
0°-90°	6251.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6251.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3905	
5°	3926	377
15°	4011	1132
25°	3742	1707
35°	2835	1747
45°	1311	1018
55°	227	234
65°	21	29
75°	7	7
85°	0	0
90°	0	



TEST NUMBER: P205244

CATALOG NUMBER: LD6B60D010TE EU6B60708040 6LBWLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	3905.1
2.5°	3898.0
5°	3926.4
7.5°	3954.7
10°	3990.2
12.5°	3997.3
15°	4011.4
17.5°	3997.3
20°	3961.8
22.5°	3848.4
25°	3742.1
27.5°	3572.0
30°	3352.3
32.5°	3125.5
35°	2834.9
37.5°	2508.9
40°	2147.5
42.5°	1743.5
45°	1311.2
47.5°	914.3
50°	602.4
52.5°	382.7
55°	226.8
57.5°	120.5
60°	63.8
62.5°	35.4
65°	21.3
67.5°	21.3
70°	14.2
72.5°	7.1
75°	7.1
77.5°	7.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)