

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274403

Luminaire Tested: **LD6B10DE010W2N2765 EU6B1020W2N902765 6LBW0MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P274403
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35124)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B10DE010W2N2765 EU6B1020W2N902765 6LBW0MW
Description: PORTFOLIO 6" W2N RN DOWNLIGHT, WIDE DISTRIBUTION WITH MATTE WHITE FINISH
Light Source: W2N 2700K-6500K CCT TUNING RANGE
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 869.8 lumens
Efficiency: N/A
Efficacy: 62.1 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P274403

CATALOG NUMBER: LD6B10DE010W2N2765 EU6B1020W2N902765 6LBW0MW

Luminous Intensity Polar Plot





TEST NUMBER: P274403

CATALOG NUMBER: LD6B10DE010W2N2765 EU6B1020W2N902765 6LBW0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88			88
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			77
3	95	86	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68			68
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60			60
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54			54
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49			49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			44
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40			40
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37			37
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34			34

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	31870
5°	31782
10°	31447
15°	30928
20°	30326
25°	29161
30°	27421
35°	24785
40°	21027
45°	16940
50°	13387
55°	10555
60°	8807
65°	7981
70°	7439
75°	6655
80°	5936
85°	4716



TEST NUMBER: P274403

CATALOG NUMBER: LD6B10DE010W2N2765 EU6B1020W2N902765 6LBW0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.0	5.3
10°-20°	129.0	14.8
20°-30°	185.9	21.4
30°-40°	193.0	22.2
40°-50°	142.7	16.4
50°-60°	85.2	9.8
60°-70°	51.8	6.0
70°-80°	28.4	3.3
80°-90°	7.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	360.9	41.5
0°-40°	553.9	63.7
0°-60°	781.8	89.9
0°-90°	869.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	869.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	488	
5°	485	46
15°	458	129
25°	405	186
35°	311	193
45°	184	143
55°	93	85
65°	52	52
75°	26	28
85°	6	8
90°	0	



TEST NUMBER: P274403

CATALOG NUMBER: LD6B10DE010W2N2765 EU6B1020W2N902765 6LBW0MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	488.5
2.5°	488.5
5°	485.3
7.5°	481.1
10°	474.7
12.5°	467.4
15°	457.9
17.5°	447.3
20°	436.8
22.5°	422.0
25°	405.1
27.5°	387.2
30°	364.0
32.5°	340.8
35°	311.2
37.5°	280.6
40°	246.9
42.5°	214.2
45°	183.6
47.5°	156.1
50°	131.9
52.5°	110.8
55°	92.8
57.5°	79.1
60°	67.5
62.5°	59.1
65°	51.7
67.5°	45.4
70°	39.0
72.5°	32.7
75°	26.4
77.5°	21.1
80°	15.8
82.5°	11.6
85°	6.3
87.5°	3.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)