

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205048

Luminaire Tested: **LD6B60D010TE EU6B60709040 6LBCSMMS1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205048
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709040 6LBCSMMS1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5329.6 lumens
Efficiency: N/A
Efficacy: 85.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205048

CATALOG NUMBER: LD6B60D010TE EU6B60709040 6LBCSMMS1

Luminous Intensity Polar Plot





TEST NUMBER: P205048

CATALOG NUMBER: LD6B60D010TE EU6B60709040 6LBCSMMS1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	103	100	108	105	101	98	100	98	95		97	94	92		93
2	102	95	89	84	99	93	88	83	90	85	81		86	83	79		83
3	94	85	77	72	92	83	76	71	80	74	70		77	73	69		75
4	87	76	68	62	84	74	67	61	72	66	61		70	64	60		68
5	80	68	60	54	78	67	59	54	65	58	53		63	57	53		61
6	74	62	54	48	72	61	53	47	59	52	47		58	51	47		56
7	69	56	48	42	67	56	48	42	54	47	42		53	46	42		51
8	64	52	44	38	63	51	43	38	50	43	38		48	42	38		47
9	60	48	40	35	59	47	40	34	46	39	34		45	39	34		44
10	57	44	36	31	55	43	36	31	43	36	31		42	35	31		41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205048

CATALOG NUMBER: LD6B60D010TE EU6B60709040 6LBCSMMS1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	230.7	4.3
10°-20°	647.2	12.1
20°-30°	945.3	17.7
30°-40°	1081.2	20.3
40°-50°	1039.1	19.5
50°-60°	802.4	15.1
60°-70°	447.8	8.4
70°-80°	130.3	2.4
80°-90°	5.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1823.2	34.2
0°-40°	2904.4	54.5
0°-60°	4745.8	89.0
0°-90°	5329.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5329.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2448	
5°	2427	231
15°	2296	647
25°	2054	945
35°	1730	1081
45°	1355	1039
55°	900	802
65°	448	448
75°	114	130
85°	3	6
90°	0	



TEST NUMBER: P205048

CATALOG NUMBER: LD6B60D010TE EU6B60709040 6LBCSMMS1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2447.5
2.5°	2447.5
5°	2426.8
7.5°	2416.5
10°	2382.0
12.5°	2340.7
15°	2295.8
17.5°	2251.0
20°	2185.5
22.5°	2133.8
25°	2054.5
27.5°	1975.3
30°	1896.0
32.5°	1816.7
35°	1730.5
37.5°	1644.3
40°	1544.3
42.5°	1454.7
45°	1354.8
47.5°	1241.0
50°	1134.1
52.5°	1016.9
55°	899.7
57.5°	779.1
60°	665.3
62.5°	551.6
65°	448.1
67.5°	351.6
70°	262.0
72.5°	182.7
75°	113.8
77.5°	58.6
80°	20.7
82.5°	6.9
85°	3.4
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)