

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274383

Luminaire Tested: **LD6B15DE010W2N2050 EU6B1020W2N902050 6LBM0LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P274383
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35220)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B15DE010W2N2050 EU6B1020W2N902050 6LBM0LI
Description: PORTFOLIO 6" W2N RN DOWNLIGHT, MEDIUM DISTRIBUTION WITH SPECULAR FINISH
Light Source: W2N 2000K-5000K CCT TUNING RANGE
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1201.5 lumens
Efficiency: N/A
Efficacy: 54.6 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.84
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 22
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P274383

CATALOG NUMBER: LD6B15DE010W2N2050 EU6B1020W2N902050 6LBM0LI

Luminous Intensity Polar Plot





TEST NUMBER: P274383

CATALOG NUMBER: LD6B15DE010W2N2050 EU6B1020W2N902050 6LBM0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94		
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82		
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	84	80	78	76		
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	71		
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67		
7	84	75	69	65	83	75	69	65	73	68	65	72	68	65	71	67	64	63		
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	68	63	60	59		
9	77	67	62	58	76	67	61	58	66	61	57	65	60	57	64	60	57	56		
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	100588
5°	99603
10°	93932
15°	84509
20°	73690
25°	62656
30°	49268
35°	30512
40°	15475
45°	6191
50°	2111
55°	785
60°	600
65°	355
70°	229
75°	302
80°	0
85°	0



TEST NUMBER: P274383

CATALOG NUMBER: LD6B15DE010W2N2050 EU6B1020W2N902050 6LBM0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.8	11.8
10°-20°	348.1	29.0
20°-30°	395.5	32.9
30°-40°	244.4	20.3
40°-50°	60.3	5.0
50°-60°	7.9	0.7
60°-70°	2.7	0.2
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	885.4	73.7
0°-40°	1129.8	94.0
0°-60°	1198.0	99.7
0°-90°	1201.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1201.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1542	
5°	1521	142
15°	1251	348
25°	870	395
35°	383	244
45°	67	60
55°	7	8
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P274383

CATALOG NUMBER: LD6B15DE010W2N2050 EU6B1020W2N902050 6LBM0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1541.8
2.5°	1537.1
5°	1520.9
7.5°	1480.4
10°	1417.9
12.5°	1339.2
15°	1251.2
17.5°	1155.2
20°	1061.4
22.5°	965.3
25°	870.4
27.5°	770.9
30°	654.0
32.5°	520.9
35°	383.1
37.5°	272.0
40°	181.7
42.5°	113.4
45°	67.1
47.5°	38.2
50°	20.8
52.5°	10.4
55°	6.9
57.5°	5.8
60°	4.6
62.5°	3.5
65°	2.3
67.5°	2.3
70°	1.2
72.5°	1.2
75°	1.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)