

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274371

Luminaire Tested: **LD6B15DE010W2N2050 EU6B1020W2N902050 6LBN0MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P274371
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35208)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B15DE010W2N2050 EU6B1020W2N902050 6LBN0MB
Description: PORTFOLIO 6" W2N RN DOWNLIGHT, NARROW DISTRIBUTION WITH MATTE BLACK FINISH
Light Source: W2N 2000K-5000K CCT TUNING RANGE
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 580.5 lumens
Efficiency: N/A
Efficacy: 26.4 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.79
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 22
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P274371

CATALOG NUMBER: LD6B15DE010W2N2050 EU6B1020W2N902050 6LBN0MB

Luminous Intensity Polar Plot





TEST NUMBER: P274371

CATALOG NUMBER: LD6B15DE010W2N2050 EU6B1020W2N902050 6LBN0MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88			
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83			
4	99	92	86	82	97	90	86	82	88	84	81	86	83	80	85	82	79	78			
5	94	86	81	77	92	85	80	76	84	79	76	82	78	75	80	77	74	73			
6	90	81	76	72	88	81	75	71	79	74	71	78	74	70	76	73	70	69			
7	86	77	71	67	84	76	71	67	75	70	67	74	69	66	73	69	66	65			
8	82	73	67	63	80	72	67	63	71	66	63	70	66	62	69	65	62	61			
9	78	69	63	60	77	68	63	59	67	63	59	67	62	59	66	62	59	58			
10	75	65	60	56	74	65	60	56	64	59	56	63	59	56	63	59	56	54			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52035
5°	48404
10°	40736
15°	33825
20°	29222
25°	25985
30°	21282
35°	13070
40°	5224
45°	1186
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P274371

CATALOG NUMBER: LD6B15DE010W2N2050 EU6B1020W2N902050 6LBN0MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	13.6
10°-20°	167.7	28.9
20°-30°	194.6	33.5
30°-40°	121.9	21.0
40°-50°	17.2	3.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	441.5	76.0
0°-40°	563.3	97.0
0°-60°	580.5	100.0
0°-90°	580.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	580.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	949	
5°	880	79
15°	596	168
25°	430	195
35°	195	122
45°	15	17
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P274371

CATALOG NUMBER: LD6B15DE010W2N2050 EU6B1020W2N902050 6LBN0MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	949.2
2.5°	930.5
5°	879.6
7.5°	806.6
10°	731.8
12.5°	660.5
15°	596.0
17.5°	541.7
20°	500.9
22.5°	463.6
25°	429.6
27.5°	388.8
30°	336.2
32.5°	270.0
35°	195.3
37.5°	127.4
40°	73.0
42.5°	37.4
45°	15.3
47.5°	3.4
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)