

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274395

Luminaire Tested: **LD6B15DE010W2N2050 EU6B1020W2N902050 6LBW0LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P274395
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35285)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B15DE010W2N2050 EU6B1020W2N902050 6LBW0LI
Description: PORTFOLIO 6" W2N RN DOWNLIGHT, WIDE DISTRIBUTION WITH SPECULAR FINISH
Light Source: W2N 2000K-5000K CCT TUNING RANGE
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1350.0 lumens
Efficiency: N/A
Efficacy: 61.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 22
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P274395

CATALOG NUMBER: LD6B15DE010W2N2050 EU6B1020W2N902050 6LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P274395

CATALOG NUMBER: LD6B15DE010W2N2050 EU6B1020W2N902050 6LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92			92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76			76
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69			69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63			63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57			57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44			44
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41			41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55024
5°	55535
10°	57085
15°	58512
20°	59402
25°	58178
30°	54541
35°	48758
40°	39500
45°	26129
50°	13205
55°	5573
60°	1801
65°	710
70°	591
75°	378
80°	0
85°	0



TEST NUMBER: P274395

CATALOG NUMBER: LD6B15DE010W2N2050 EU6B1020W2N902050 6LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.4	6.0
10°-20°	244.5	18.1
20°-30°	368.6	27.3
30°-40°	377.3	27.9
40°-50°	219.8	16.3
50°-60°	50.5	3.7
60°-70°	6.2	0.5
70°-80°	1.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	694.5	51.4
0°-40°	1071.8	79.4
0°-60°	1342.2	99.4
0°-90°	1350.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1350.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	843	
5°	848	81
15°	866	245
25°	808	369
35°	612	377
45°	283	220
55°	49	51
65°	5	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P274395

CATALOG NUMBER: LD6B15DE010W2N2050 EU6B1020W2N902050 6LBW0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	843.4
2.5°	841.8
5°	848.0
7.5°	854.1
10°	861.7
12.5°	863.3
15°	866.3
17.5°	863.3
20°	855.6
22.5°	831.1
25°	808.2
27.5°	771.4
30°	724.0
32.5°	675.0
35°	612.2
37.5°	541.8
40°	463.8
42.5°	376.5
45°	283.2
47.5°	197.4
50°	130.1
52.5°	82.7
55°	49.0
57.5°	26.0
60°	13.8
62.5°	7.7
65°	4.6
67.5°	4.6
70°	3.1
72.5°	1.5
75°	1.5
77.5°	1.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)