

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205149

Luminaire Tested: **LD6B60D010TE EU6B60709040 6LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205149
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709040 6LBMLI1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4636.8 lumens
Efficiency: N/A
Efficacy: 74.2 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205149

CATALOG NUMBER: LD6B60D010TE EU6B60709040 6LBMLI1

Luminous Intensity Polar Plot






TEST NUMBER: P205149

CATALOG NUMBER: LD6B60D010TE EU6B60709040 6LBMLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	106	111	109	107	105		105	103	101		101	100	98		98	97	96
2	108	103	100	96	106	102	98	95		99	96	93		96	93	91		93	91	89
3	103	97	92	88	101	95	91	87		93	89	86		90	87	85		88	85	83
4	98	91	85	81	96	89	84	81		87	83	80		85	82	79		83	80	78
5	93	85	79	75	91	84	79	75		82	78	74		81	77	73		79	76	73
6	89	80	74	70	87	79	74	70		78	73	69		76	72	69		75	71	68
7	84	75	69	65	83	75	69	65		73	68	65		72	68	64		71	67	64
8	80	71	65	61	79	70	65	61		69	64	61		68	64	60		67	63	60
9	77	67	61	57	75	67	61	57		66	61	57		65	60	57		64	60	57
10	73	64	58	54	72	63	58	54		62	57	54		62	57	54		61	57	54

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205149

CATALOG NUMBER: LD6B60D010TE EU6B60709040 6LBMLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	534.6	11.5
10°-20°	1330.9	28.7
20°-30°	1547.1	33.4
30°-40°	947.4	20.4
40°-50°	235.3	5.1
50°-60°	27.5	0.6
60°-70°	10.2	0.2
70°-80°	3.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3412.5	73.6
0°-40°	4359.9	94.0
0°-60°	4622.6	99.7
0°-90°	4636.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4636.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5803	
5°	5726	535
15°	4776	1331
25°	3424	1547
35°	1483	947
45°	261	235
55°	24	28
65°	12	10
75°	6	4
85°	0	0
90°	0	



TEST NUMBER: P205149

CATALOG NUMBER: LD6B60D010TE EU6B60709040 6LBMLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	5802.8
2.5°	5796.8
5°	5725.6
7.5°	5571.4
10°	5363.7
12.5°	5090.8
15°	4776.3
17.5°	4438.1
20°	4105.8
22.5°	3773.6
25°	3423.5
27.5°	3020.0
30°	2557.3
32.5°	2017.3
35°	1483.3
37.5°	1044.3
40°	712.0
42.5°	445.0
45°	261.1
47.5°	148.3
50°	77.1
52.5°	35.6
55°	23.7
57.5°	17.8
60°	17.8
62.5°	11.9
65°	11.9
67.5°	5.9
70°	5.9
72.5°	5.9
75°	5.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)