

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274375

Luminaire Tested: **LD6B20DE010W2N2765 EU6B1020W2N902765 6LBN0H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P274375
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1808-906-17)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20DE010W2N2765 EU6B1020W2N902765 6LBN0H
Description: PORTFOLIO 6" W2N RN DOWNLIGHT, NARROW DISTRIBUTION WITH HAZE FINISH
Light Source: W2N 2700K-6500K CCT TUNING RANGE
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1153.0 lumens
Efficiency: N/A
Efficacy: 41.2 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.77
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P274375

CATALOG NUMBER: LD6B20DE010W2N2765 EU6B1020W2N902765 6LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P274375

CATALOG NUMBER: LD6B20DE010W2N2765 EU6B1020W2N902765 6LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88			
3	103	97	93	89	101	96	92	88	93	90	87	91	88	85	89	86	84	83			
4	99	91	86	82	97	90	85	82	88	84	81	86	83	80	84	81	79	77			
5	94	86	81	76	92	85	80	76	83	79	75	82	78	75	80	77	74	73			
6	90	81	75	71	88	80	75	71	79	74	71	78	73	70	76	73	70	68			
7	85	77	71	67	84	76	71	67	75	70	66	74	69	66	73	69	66	64			
8	82	73	67	63	80	72	67	63	71	66	63	70	66	62	69	65	62	61			
9	78	69	63	59	77	68	63	59	67	63	59	67	62	59	66	62	59	58			
10	75	65	60	56	74	65	60	56	64	59	56	63	59	56	63	59	56	55			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	98161
5°	93792
10°	83877
15°	72475
20°	60456
25°	49104
30°	37177
35°	22118
40°	10928
45°	4318
50°	1075
55°	688
60°	395
65°	233
70°	289
75°	0
80°	0
85°	0



TEST NUMBER: P274375

CATALOG NUMBER: LD6B20DE010W2N2765 EU6B1020W2N902765 6LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.2	13.6
10°-20°	354.3	30.7
20°-30°	370.6	32.1
30°-40°	212.1	18.4
40°-50°	49.7	4.3
50°-60°	7.0	0.6
60°-70°	2.4	0.2
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	881.2	76.4
0°-40°	1093.3	94.8
0°-60°	1149.9	99.7
0°-90°	1153.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1153.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1791	
5°	1704	156
15°	1277	354
25°	812	371
35°	330	212
45°	56	50
55°	7	7
65°	2	2
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P274375

CATALOG NUMBER: LD6B20DE010W2N2765 EU6B1020W2N902765 6LBN0H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1790.6
2.5°	1767.3
5°	1704.4
7.5°	1611.0
10°	1506.8
12.5°	1395.5
15°	1277.0
17.5°	1153.0
20°	1036.3
22.5°	923.1
25°	811.8
27.5°	707.6
30°	587.3
32.5°	454.4
35°	330.5
37.5°	229.9
40°	152.7
42.5°	97.0
45°	55.7
47.5°	28.7
50°	12.6
52.5°	10.8
55°	7.2
57.5°	5.4
60°	3.6
62.5°	3.6
65°	1.8
67.5°	1.8
70°	1.8
72.5°	1.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)