

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204326

Luminaire Tested: **LD6B60D010TE EU6B60709040 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204326
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709040 6LBSWH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5426.4 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204326

CATALOG NUMBER: LD6B60D010TE EU6B60709040 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204326

CATALOG NUMBER: LD6B60D010TE EU6B60709040 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	101	108	105	102	99	101	98	96		97	95	93		94
2	103	96	90	85	100	94	89	84	91	86	83		87	84	81		85
3	95	86	79	73	93	84	78	73	82	76	72		79	74	70		76
4	88	77	70	64	86	76	69	63	74	68	63		72	66	62		69
5	81	70	62	56	79	69	62	56	67	60	55		65	59	55		63
6	76	64	56	50	74	63	55	50	61	54	49		60	54	49		58
7	71	58	51	45	69	58	50	45	56	49	45		55	49	44		54
8	66	54	46	41	65	53	46	41	52	45	40		51	45	40		50
9	62	50	42	37	61	49	42	37	48	41	37		47	41	37		46
10	58	46	39	34	57	46	39	34	45	38	34		44	38	34		43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204326

CATALOG NUMBER: LD6B60D010TE EU6B60709040 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	298.5	5.5
10°-20°	772.6	14.2
20°-30°	1010.5	18.6
30°-40°	1070.0	19.7
40°-50°	998.0	18.4
50°-60°	755.9	13.9
60°-70°	409.4	7.5
70°-80°	109.8	2.0
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2081.6	38.4
0°-40°	3151.7	58.1
0°-60°	4905.5	90.4
0°-90°	5426.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5426.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3236	
5°	3189	298
15°	2761	773
25°	2197	1011
35°	1710	1070
45°	1300	998
55°	849	756
65°	410	409
75°	95	110
85°	0	2
90°	0	



TEST NUMBER: P204326

CATALOG NUMBER: LD6B60D010TE EU6B60709040 6LBSWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	3236.3
2.5°	3224.4
5°	3188.8
7.5°	3111.6
10°	3010.6
12.5°	2891.9
15°	2761.2
17.5°	2612.8
20°	2482.1
22.5°	2333.7
25°	2197.1
27.5°	2060.5
30°	1929.9
32.5°	1817.1
35°	1710.2
37.5°	1603.3
40°	1502.3
42.5°	1401.4
45°	1300.4
47.5°	1187.6
50°	1074.8
52.5°	962.0
55°	849.1
57.5°	730.4
60°	617.6
62.5°	510.7
65°	409.7
67.5°	314.7
70°	231.6
72.5°	160.3
75°	95.0
77.5°	41.6
80°	11.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)