

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274369

Luminaire Tested: **LD6B20DE010W2N2765 EU6B1020W2N902765 6LBN0MB**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P274369  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35208)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B20DE010W2N2765 EU6B1020W2N902765 6LBN0MB  
Description: PORTFOLIO 6" W2N RN DOWNLIGHT, NARROW DISTRIBUTION WITH MATTE BLACK FINISH  
Light Source: W2N 2700K-6500K CCT TUNING RANGE  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 799.7 lumens  
Efficiency: N/A  
Efficacy: 28.6 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.79  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P274369

CATALOG NUMBER: LD6B20DE010W2N2765 EU6B1020W2N902765 6LBN0MB

### Luminous Intensity Polar Plot





TEST NUMBER: P274369

CATALOG NUMBER: LD6B20DE010W2N2765 EU6B1020W2N902765 6LBN0MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88			
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83			
4	99	92	86	82	97	90	86	82	88	84	81	86	83	80	85	82	79	78			
5	94	86	81	77	92	85	80	76	84	79	76	82	78	75	80	77	74	73			
6	90	81	76	72	88	81	75	71	79	74	71	78	74	70	76	73	70	69			
7	86	77	71	67	84	76	71	67	75	70	67	74	69	66	73	69	66	65			
8	82	73	67	63	80	72	67	63	71	66	63	70	66	62	69	65	62	61			
9	78	69	63	60	77	68	63	59	67	63	59	67	62	59	66	62	59	58			
10	75	65	60	56	74	65	60	56	64	59	56	63	59	56	63	59	56	54			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	71683
5°	66679
10°	56122
15°	46595
20°	40253
25°	35796
30°	29315
35°	18002
40°	7199
45°	1636
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P274369

CATALOG NUMBER: LD6B20DE010W2N2765 EU6B1020W2N902765 6LBN0MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.9	13.6
10°-20°	231.1	28.9
20°-30°	268.1	33.5
30°-40°	167.9	21.0
40°-50°	23.7	3.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	608.1	76.0
0°-40°	776.0	97.0
0°-60°	799.7	100.0
0°-90°	799.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	799.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1308	
5°	1212	109
15°	821	231
25°	592	268
35°	269	168
45°	21	24
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P274369

CATALOG NUMBER: LD6B20DE010W2N2765 EU6B1020W2N902765 6LBN0MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1307.6
2.5°	1281.8
5°	1211.7
7.5°	1111.1
10°	1008.2
12.5°	909.9
15°	821.0
17.5°	746.2
20°	690.0
22.5°	638.6
25°	591.8
27.5°	535.7
30°	463.1
32.5°	371.9
35°	269.0
37.5°	175.4
40°	100.6
42.5°	51.5
45°	21.1
47.5°	4.7
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)