

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P683872

Luminaire Tested: **LX6C10D010 EX6C109027 6LBSH**

Issue Date: 2/15/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P683872
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C10D010 EX6C109027 6LBSH
Description: 6 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 6LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1032.0 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P683872

CATALOG NUMBER: LX6C10D010 EX6C109027 6LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P683872

CATALOG NUMBER: LX6C10D010 EX6C109027 6LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	29586
5°	29452
10°	28840
15°	27792
20°	26515
25°	25084
30°	23662
35°	22279
40°	20982
45°	19560
50°	17833
55°	15751
60°	13332
65°	10468
70°	7469
75°	4088
80°	726
85°	0



TEST NUMBER: P683872

CATALOG NUMBER: LX6C10D010 EX6C109027 6LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.6	4.9
10°-20°	137.4	13.3
20°-30°	190.8	18.5
30°-40°	208.2	20.2
40°-50°	194.3	18.8
50°-60°	147.5	14.3
60°-70°	80.7	7.8
70°-80°	22.2	2.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	378.8	36.7
0°-40°	587.0	56.9
0°-60°	928.8	90.0
0°-90°	1032.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1032.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	540	
5°	535	51
15°	490	137
25°	415	191
35°	333	208
45°	252	194
55°	165	147
65°	81	81
75°	19	22
85°	0	0
90°	0	



TEST NUMBER: P683872

CATALOG NUMBER: LX6C10D010 EX6C109027 6LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	539.7
2.5°	539.7
5°	535.2
7.5°	528.4
10°	518.1
12.5°	504.5
15°	489.7
17.5°	471.5
20°	454.5
22.5°	434.1
25°	414.7
27.5°	395.4
30°	373.8
32.5°	353.4
35°	332.9
37.5°	312.5
40°	293.2
42.5°	272.7
45°	252.3
47.5°	231.8
50°	209.1
52.5°	187.5
55°	164.8
57.5°	143.2
60°	121.6
62.5°	100.0
65°	80.7
67.5°	62.5
70°	46.6
72.5°	31.8
75°	19.3
77.5°	9.1
80°	2.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)