

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684745

Luminaire Tested: **LX6C10D010 EX6109035 6LRMDLI**

Issue Date: 2/15/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P684745
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-20)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C10D010 EX6109035 6LRMDLI
Description: 6 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 6LRMD45 TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 784.0 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684745
CATALOG NUMBER: LX6C10D010 EX6109035 6LRMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P684745

CATALOG NUMBER: LX6C10D010 EX6109035 6LRMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89			
3	104	98	93	90	102	97	92	89	94	90	87	92	89	86	89	87	85	83			
4	99	92	87	83	97	91	86	83	89	85	82	87	83	81	85	82	80	78			
5	95	87	81	77	93	86	81	77	84	80	76	83	79	76	81	78	75	74			
6	90	82	77	73	89	81	76	72	80	75	72	79	74	71	77	74	71	70			
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66			
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62			
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59			
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	64194
5°	64319
10°	61294
15°	52781
20°	43480
25°	33958
30°	24523
35°	12561
40°	6126
45°	2543
50°	461
55°	268
60°	175
65°	130
70°	96
75°	85
80°	63
85°	0



TEST NUMBER: P684745

CATALOG NUMBER: LX6C10D010 EX6109035 6LRMDLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.6	14.0
10°-20°	257.8	32.9
20°-30°	255.3	32.6
30°-40°	129.4	16.5
40°-50°	27.9	3.6
50°-60°	2.6	0.3
60°-70°	1.0	0.1
70°-80°	0.4	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	622.6	79.4
0°-40°	752.0	95.9
0°-60°	782.5	99.8
0°-90°	784.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	784.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1171	
5°	1169	110
15°	930	258
25°	561	255
35°	188	129
45°	33	28
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P684745

CATALOG NUMBER: LX6C10D010 EX6109035 6LRMDLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1171.0
2.5°	1172.4
5°	1168.8
7.5°	1150.5
10°	1101.1
12.5°	1021.8
15°	930.0
17.5°	835.9
20°	745.3
22.5°	654.7
25°	561.4
27.5°	466.4
30°	387.4
32.5°	298.4
35°	187.7
37.5°	126.3
40°	85.6
42.5°	55.4
45°	32.8
47.5°	14.7
50°	5.4
52.5°	3.6
55°	2.8
57.5°	2.0
60°	1.6
62.5°	1.2
65°	1.0
67.5°	0.8
70°	0.6
72.5°	0.4
75°	0.4
77.5°	0.2
80°	0.2
82.5°	0.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)