

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P582946

Luminaire Tested: **LX6C10D010 EU6109040 6LBHYLI**

Issue Date: 8/31/2023

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P582946  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2301-896-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/31/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C10D010 EU6109040 6LBHYLI  
Description: 6 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS  
AND 6LCHYP TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 690.0 lumens  
Efficiency: N/A  
Efficacy: 70.8 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.52  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.75  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P582946

CATALOG NUMBER: LX6C10D010 EU6109040 6LBHYLI

### Luminous Intensity Polar Plot





TEST NUMBER: P582946

CATALOG NUMBER: LX6C10D010 EU6109040 6LBHYLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85			
5	100	94	89	86	98	93	89	86	91	88	85	89	86	84	88	85	83	82			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79			
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	76			
8	91	83	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	74			
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	72	71			
10	85	78	74	71	84	78	73	71	77	73	70	76	73	70	76	72	70	69			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	117014
5°	114060
10°	96703
15°	62679
20°	38923
25°	20947
30°	7204
35°	2898
40°	773
45°	349
50°	136
55°	57
60°	33
65°	39
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P582946

CATALOG NUMBER: LX6C10D010 EU6109040 6LBHYLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	187.0	27.1
10°-20°	308.3	44.7
20°-30°	159.9	23.2
30°-40°	30.3	4.4
40°-50°	3.8	0.6
50°-60°	0.5	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	655.1	95.0
0°-40°	685.4	99.3
0°-60°	689.8	100.0
0°-90°	690.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	690.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2134	
5°	2073	187
15°	1104	308
25°	346	160
35°	43	30
45°	4	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P582946

CATALOG NUMBER: LX6C10D010 EU6109040 6LBHYLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2134.5
2.5°	2131.0
5°	2072.7
7.5°	1938.9
10°	1737.2
12.5°	1433.5
15°	1104.4
17.5°	838.6
20°	667.2
22.5°	497.4
25°	346.3
27.5°	212.8
30°	113.8
32.5°	76.8
35°	43.3
37.5°	18.8
40°	10.8
42.5°	7.0
45°	4.5
47.5°	2.5
50°	1.6
52.5°	0.6
55°	0.6
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)