

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204115

Luminaire Tested: **LD6B60D010TE EU6B60708050 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204115
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60708050 6LBNMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4462.5 lumens
Efficiency: N/A
Efficacy: 71.4 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204115

CATALOG NUMBER: LD6B60D010TE EU6B60708050 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204115

CATALOG NUMBER: LD6B60D010TE EU6B60708050 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20				20
RC	80				70					50					30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90	90
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81	81
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73	73
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66	66
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61	61
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47	47
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44	44
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41	41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204115

CATALOG NUMBER: LD6B60D010TE EU6B60708050 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	339.8	7.6
10°-20°	900.8	20.2
20°-30°	1202.6	26.9
30°-40°	970.2	21.7
40°-50°	465.0	10.4
50°-60°	275.6	6.2
60°-70°	183.2	4.1
70°-80°	98.2	2.2
80°-90°	27.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2443.2	54.8
0°-40°	3413.5	76.5
0°-60°	4154.1	93.1
0°-90°	4462.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4462.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3660	
5°	3617	340
15°	3206	901
25°	2631	1203
35°	1553	970
45°	574	465
55°	305	276
65°	184	183
75°	92	98
85°	21	27
90°	0	



TEST NUMBER: P204115

CATALOG NUMBER: LD6B60D010TE EU6B60708050 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3659.7
2.5°	3659.7
5°	3617.2
7.5°	3546.2
10°	3446.9
12.5°	3340.6
15°	3205.8
17.5°	3078.1
20°	2936.3
22.5°	2787.3
25°	2631.3
27.5°	2468.2
30°	2234.1
32.5°	1907.9
35°	1553.3
37.5°	1227.0
40°	950.4
42.5°	737.6
45°	574.5
47.5°	453.9
50°	383.0
52.5°	340.4
55°	305.0
57.5°	276.6
60°	241.1
62.5°	212.8
65°	184.4
67.5°	156.0
70°	134.8
72.5°	113.5
75°	92.2
77.5°	70.9
80°	56.7
82.5°	42.6
85°	21.3
87.5°	7.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)