

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204631

Luminaire Tested: **LD6B60D010TE EU6B60708050 6LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204631
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60708050 6LB5MW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6714.9 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204631

CATALOG NUMBER: LD6B60D010TE EU6B60708050 6LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204631

CATALOG NUMBER: LD6B60D010TE EU6B60708050 6LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	110	106	102	99	107	104	100	97		99	97	94		96	93	91		92	90	88
2	101	93	87	82	98	92	86	81		88	83	79		85	81	77		82	79	76
3	93	83	75	69	90	81	74	69		78	72	67		76	70	66		73	69	65
4	85	74	66	59	83	72	65	59		70	63	58		68	62	57		66	61	56
5	78	66	58	51	76	65	57	51		63	56	51		61	55	50		59	54	49
6	73	60	51	45	71	59	51	45		57	50	44		55	49	44		54	48	44
7	67	54	46	40	66	54	46	40		52	45	40		51	44	39		49	43	39
8	63	50	41	36	61	49	41	36		48	41	35		46	40	35		45	39	35
9	59	46	38	32	57	45	37	32		44	37	32		43	36	32		42	36	32
10	55	42	34	29	54	42	34	29		41	34	29		40	33	29		39	33	29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204631

CATALOG NUMBER: LD6B60D010TE EU6B60708050 6LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.3	3.8
10°-20°	730.7	10.9
20°-30°	1100.5	16.4
30°-40°	1309.4	19.5
40°-50°	1307.1	19.5
50°-60°	1062.9	15.8
60°-70°	654.0	9.7
70°-80°	253.4	3.8
80°-90°	40.6	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2087.5	31.1
0°-40°	3396.9	50.6
0°-60°	5767.0	85.9
0°-90°	6714.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6714.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2705	
5°	2698	256
15°	2594	731
25°	2395	1100
35°	2097	1309
45°	1699	1307
55°	1190	1063
65°	656	654
75°	231	253
85°	32	41
90°	0	



TEST NUMBER: P204631

CATALOG NUMBER: LD6B60D010TE EU6B60708050 6LBSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2705.4
2.5°	2709.4
5°	2697.5
7.5°	2681.6
10°	2661.7
12.5°	2625.9
15°	2594.0
17.5°	2546.3
20°	2494.6
22.5°	2446.8
25°	2395.1
27.5°	2323.5
30°	2251.9
32.5°	2184.2
35°	2096.7
37.5°	2001.2
40°	1913.7
42.5°	1806.3
45°	1698.9
47.5°	1583.5
50°	1460.1
52.5°	1332.8
55°	1189.6
57.5°	1050.3
60°	915.1
62.5°	783.8
65°	656.5
67.5°	537.1
70°	425.7
72.5°	322.3
75°	230.8
77.5°	151.2
80°	91.5
82.5°	55.7
85°	31.8
87.5°	15.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)