

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563896

Luminaire Tested: **LX6C10D010 EX6C109030 6LBMH**

Issue Date: 2/15/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P563896  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C10D010 EX6C109030 6LBMH  
Description: 6 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 6LBM TRIM WITH H FINISH, DIM TO WARM  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 766.0 lumens  
Efficiency: N/A  
Efficacy: 78.2 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.8  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P563896

CATALOG NUMBER: LX6C10D010 EX6C109030 6LBMH

### Luminous Intensity Polar Plot





TEST NUMBER: P563896

CATALOG NUMBER: LX6C10D010 EX6C109030 6LBMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53			53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49			49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46			46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	41554
5°	40810
10°	38727
15°	36311
20°	33819
25°	31163
30°	25960
35°	18297
40°	11665
45°	6954
50°	4102
55°	2619
60°	1798
65°	1284
70°	882
75°	699
80°	347
85°	0



TEST NUMBER: P563896

CATALOG NUMBER: LX6C10D010 EX6C109030 6LBMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	69.3	9.0
10°-20°	179.3	23.4
20°-30°	232.3	30.3
30°-40°	172.5	22.5
40°-50°	72.8	9.5
50°-60°	25.9	3.4
60°-70°	10.0	1.3
70°-80°	3.5	0.5
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	480.9	62.8
0°-40°	653.4	85.3
0°-60°	752.1	98.2
0°-90°	766.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	766.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	758	
5°	742	69
15°	640	179
25°	515	232
35°	273	172
45°	90	73
55°	27	26
65°	10	10
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P563896

CATALOG NUMBER: LX6C10D010 EX6C109030 6LBMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	758.0
2.5°	755.8
5°	741.6
7.5°	720.8
10°	695.7
12.5°	668.3
15°	639.8
17.5°	608.2
20°	579.7
22.5°	550.2
25°	515.2
27.5°	467.0
30°	410.1
32.5°	343.4
35°	273.4
37.5°	214.4
40°	163.0
42.5°	121.4
45°	89.7
47.5°	65.6
50°	48.1
52.5°	36.1
55°	27.4
57.5°	20.8
60°	16.4
62.5°	12.0
65°	9.9
67.5°	7.6
70°	5.5
72.5°	4.4
75°	3.3
77.5°	2.2
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)