

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563899

Luminaire Tested: **LX6C10D010 EX6C109030 6LBWH**

Issue Date: 2/15/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P563899
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C10D010 EX6C109030 6LBWH
Description: 6 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBW TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 911.1 lumens
Efficiency: N/A
Efficacy: 93.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P563899

CATALOG NUMBER: LX6C10D010 EX6C109030 6LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P563899

CATALOG NUMBER: LX6C10D010 EX6C109030 6LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	30803
5°	30789
10°	30555
15°	30352
20°	29887
25°	29203
30°	27498
35°	24889
40°	20782
45°	15924
50°	11275
55°	7111
60°	4013
65°	2607
70°	1699
75°	1250
80°	758
85°	755



TEST NUMBER: P563899

CATALOG NUMBER: LX6C10D010 EX6C109030 6LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.1	5.8
10°-20°	150.6	16.5
20°-30°	220.8	24.2
30°-40°	229.8	25.2
40°-50°	159.0	17.4
50°-60°	69.2	7.6
60°-70°	21.3	2.3
70°-80°	6.4	0.7
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	424.5	46.6
0°-40°	654.3	71.8
0°-60°	882.5	96.9
0°-90°	911.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	911.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	562	
5°	560	53
15°	535	151
25°	483	221
35°	372	230
45°	205	159
55°	74	69
65°	20	21
75°	6	6
85°	1	1
90°	0	



TEST NUMBER: P563899

CATALOG NUMBER: LX6C10D010 EX6C109030 6LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	561.9
2.5°	563.1
5°	559.5
7.5°	554.8
10°	548.9
12.5°	543.0
15°	534.8
17.5°	524.1
20°	512.3
22.5°	499.3
25°	482.8
27.5°	461.6
30°	434.4
32.5°	406.1
35°	371.9
37.5°	334.1
40°	290.4
42.5°	246.7
45°	205.4
47.5°	166.4
50°	132.2
52.5°	100.4
55°	74.4
57.5°	53.1
60°	36.6
62.5°	27.2
65°	20.1
67.5°	15.4
70°	10.6
72.5°	8.3
75°	5.9
77.5°	3.5
80°	2.4
82.5°	1.2
85°	1.2
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)