

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684772

Luminaire Tested: **LX6C100D010 EX61009030 6LBNLI**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P684772
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C100D010 EX61009030 6LBNLI
Description: 6 INCH 10000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBN TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8235.0 lumens
Efficiency: N/A
Efficacy: 72.0 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 114.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684772

CATALOG NUMBER: LX6C100D010 EX61009030 6LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P684772

CATALOG NUMBER: LX6C100D010 EX61009030 6LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1027829
5°	961196
10°	783931
15°	576871
20°	397617
25°	295190
30°	221730
35°	138270
40°	67119
45°	23026
50°	3019
55°	2284
60°	1305
65°	1544
70°	1907
75°	0
80°	0
85°	0



TEST NUMBER: P684772

CATALOG NUMBER: LX6C100D010 EX61009030 6LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1558.9	18.9
10°-20°	2798.0	34.0
20°-30°	2262.3	27.5
30°-40°	1303.2	15.8
40°-50°	275.5	3.3
50°-60°	23.8	0.3
60°-70°	11.8	0.1
70°-80°	1.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6619.1	80.4
0°-40°	7922.4	96.2
0°-60°	8221.6	99.8
0°-90°	8235.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8235.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	18749	
5°	17467	###
15°	10164	2798
25°	4880	2262
35°	2066	1303
45°	297	275
55°	24	24
65°	12	12
75°	0	2
85°	0	0
90°	0	



TEST NUMBER: P684772

CATALOG NUMBER: LX6C100D010 EX61009030 6LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	18749.1
2.5°	18523.9
5°	17466.9
7.5°	15947.0
10°	14082.8
12.5°	12171.2
15°	10164.4
17.5°	8228.9
20°	6815.7
22.5°	5735.3
25°	4880.2
27.5°	4156.0
30°	3502.8
32.5°	2778.7
35°	2066.1
37.5°	1436.7
40°	937.9
42.5°	570.1
45°	297.0
47.5°	118.6
50°	35.4
52.5°	35.4
55°	23.9
57.5°	23.9
60°	11.9
62.5°	11.9
65°	11.9
67.5°	11.9
70°	11.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)