

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684781

Luminaire Tested: **LX6C100D010 EX61009040 6LBMLI**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P684781
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C100D010 EX61009040 6LBMLI
Description: 6 INCH 10000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 6LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9411.0 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 114.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684781

CATALOG NUMBER: LX6C100D010 EX61009040 6LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P684781

CATALOG NUMBER: LX6C100D010 EX61009040 6LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	645639
5°	639499
10°	605984
15°	550173
20°	486157
25°	420302
30°	328544
35°	201479
40°	103415
45°	41082
50°	13339
55°	4597
60°	3947
65°	3152
70°	1939
75°	2563
80°	0
85°	0



TEST NUMBER: P684781

CATALOG NUMBER: LX6C100D010 EX61009040 6LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1085.0	11.5
10°-20°	2701.2	28.7
20°-30°	3140.0	33.4
30°-40°	1922.8	20.4
40°-50°	477.5	5.1
50°-60°	55.8	0.6
60°-70°	20.9	0.2
70°-80°	7.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6926.1	73.6
0°-40°	8848.9	94.0
0°-60°	9382.2	99.7
0°-90°	9411.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9411.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11777	
5°	11621	###
15°	9694	2701
25°	6949	3140
35°	3011	1923
45°	530	477
55°	48	56
65°	24	21
75°	12	8
85°	0	0
90°	0	



TEST NUMBER: P684781

CATALOG NUMBER: LX6C100D010 EX61009040 6LBMLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	11777.4
2.5°	11765.3
5°	11621.0
7.5°	11307.7
10°	10886.1
12.5°	10332.3
15°	9694.0
17.5°	9007.7
20°	8333.4
22.5°	7658.8
25°	6948.6
27.5°	6129.6
30°	5190.2
32.5°	4094.4
35°	3010.6
37.5°	2119.3
40°	1445.1
42.5°	903.0
45°	529.9
47.5°	301.2
50°	156.4
52.5°	72.4
55°	48.1
57.5°	36.0
60°	36.0
62.5°	24.3
65°	24.3
67.5°	12.1
70°	12.1
72.5°	12.1
75°	12.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)